



Southwire®

61" SIMpull® Reel Capacity Chart

WIRE SIZE	1-WIRE	1-WIRE (IN SIMpull® REEL CRADLE)	3-WIRES	3-WIRES (IN SIMpull® REEL CRADLE)	4-WIRES	4-WIRES (IN SIMpull® REEL CRADLE)
8	57,500	54,500	19,167	18,167	14,375	13,625
6	42,000	39,500	14,000	13,167	10,500	9,875
4	25,500	24,250	8,500	8,083	6,375	6,063
3	21,500	20,250	7,167	6,750	5,375	5,063
2	18,000	17,000	6,000	5,667	4,500	4,250
1	13,500	12,750	4,500	4,250	3,375	3,188
1/0	11,350	10,750	3,783	3,583	2,838	2,688
2/0	9,500	8,900	3,167	2,967	2,375	2,225
3/0	7,800	7,400	2,600	2,467	1,950	1,850
4/0	6,450	6,100	2,150	2,033	1,613	1,525
250	5,200	4,900	1,733	1,633	1,300	1,225
300	4,450	4,200	1,483	1,400	1,113	1,050
350	3,900	3,650	1,300	1,217	975	913
400	3,450	3,275	1,150	1,092	863	819
500	2,850	2,700	950	900	713	675
600	2,300	2,175	767	725	575	544
700 *AL	2,250	2,125	750	708	563	531
750	1,875	1,775	625	592	469	444
900 *AL	1,775	1,675	592	558	444	419
1000	1,450	1,360	483	453	363	340

51" SIMpull® Reel Capacity Chart

WIRE SIZE	1-WIRE	3-WIRES	4-WIRES
8	34,500	11,500	8,625
6	25,250	8,417	6,313
4	15,250	5,083	3,813
3	12,900	4,300	3,225
2	10,800	3,600	2,700
1	8,050	2,683	2,013
1/0	6,750	2,250	1,688
2/0	5,600	1,867	1,400
3/0	4,650	1,550	1,163
4/0	3,800	1,267	950
250	3,050	1,017	763
300	2,625	875	656
350	2,275	758	569
400	2,025	675	506
500	1,660	553	415
600	1,335	445	334
700 *AL	1,310	437	328
750	1,085	362	271
900 *AL	1,025	342	256
1000	835	278	209



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.