# IIII/OOds® CATALOG



### **ABOUT WOODS®**

Whether you're keeping your family and electronics safe, or powering your next home improvement project, count on Woods® to meet your needs! For more than 85 years, Woods® has been a leading developer of electrical products for consumers and professionals.

Woods Power Strips feature cord lengths and configurations to fit. Woods Surge Protectors provide many levels of protection with additional features like USB and connectivity. Our Wall Taps are ergonomically built featuring an easy pull design and charging cradle for your devices.

Woods® PRO items are perfect for medium to heavy-duty use. Protect your tools and electronics, holiday decorations and more! The Woods® PRO line provides overload protection and multiple outlets to power most applications.

When you need to get a job done right, our Yellow Jacket® line offers a variety of heavy-duty workshop-grade power strips, surge strips and adapters that come standard with overload protection, durable construction, and many premium features!

From simple adapters and USB integrated items to surge protectors and heavy-duty workshop-grade products, Woods has you covered!







# Indoor 24 Hour Mechanical Timer - 1 Polarized Outlet



- 1 Polarized Outlet
- Up to 24 on/off settings per day, repearts daily
- Programmable in 30 minutes intervals
- Never lose pins cannot be removed or lost
- CFL, LED, and incandescent compatible
- Ratings: 125V ac, 60 Hz, 15A, 1875W Resistive / 8A, 1000W Tungsten / 5A Ballas

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50000WD	50000WD	2.5	5.25	6.25	6



# Indoor 24hr Heavy Duty Mechanical Timer, 1 Grounded Outlet



- 1 Grounded Outlet
- 48 ON/OFF settings, repeat daily
- Programmable in 30 minute intervals
- Never lose pins cannot be removed or lost
- CFL, LED, and incandescent compatible
- Ratings: 125Vac, 60Hz, 1/2Hp, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50001WD	50001WD	2.5	5.25	6.25	6



# Indoor 7-Day Heavy Duty Mechanical Timer, 1 Grounded Outlet



- 1 Grounded Outlet
- 6 ON/OFF settings per day, repeats weekly
- Programmable in 2hr intervals
- Never lose pins cannot be removed or lost
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50002WD	50002WD	2.5	5.25	6.25	6





#### Indoor 7-Day Mechanical Vacation Timer, 1 Polarized Outlet



- 1 Polarized Outlet
- Pre-programmed settings, repeats weekly
- Turns plugged-in device ON and OFF twice a day at random times
- Insturction slot & manual override switch
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50003WD	50003WD	2.5	5.25	6.25	6



# **Indoor 24HR Mechanical Timer, 2 Polarized Outlets**



- 2 Polarized Outlets
- Up to 24 On/Off settings per day, repeats daily
- Programmable in 30 minute intervals
- Turns plugged-in device ON and OFF twice a day at random times
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50004WD	50004WD	2.5	5.25	6.25	6



#### Indoor 24Hr Mechanical Timer, 1 Polarized Outlet (Combo Pack)

- 1 Polarized Outlet
- Up to 24 on/off settings per day, repeat daily
- Programmable in 30 minut intervals
- Never lose pins cannot be removed or lost
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50006WD	50006WD	2.5	5.75	6.87	6



# Indoor 24Hr Heavy Duty Mechanical Timer with Nightlight, 2 Grounded Outlets



- 2 Grounded Outlets
- Up to 24 on/off settings per day, repeats daily
- Programmable in 30 minute intervals
- Nightlight turns on when absence of light is detected
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 5A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50021WD	50021WD	2.5	5.5	5.75	6



# Indoor and Outdoor Mechanical Timer Combo, 1 Polarized and 2 Grounded Outlets

- 1 Indoor Mechanical Timer with 2 Grounded Outlets
- 1 Outdoor Mechanical Timer with 1 Polarized Outlets
- Up to 24 on/off settings per day, repeats daily
- Programmable in 30 minute intervals
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 8A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
13571WD	13571WD	2.62	4.13	7.75	6



# Indoor 8-Outlet Power Strip with Built-in Timer



- 8 Grounded Outlets (4 timer and 4 switch controlled grounded outlets)
- 48 ON/OFF setting per day, repeats daily
- Programmable in 30 minute intervals
- 3 ft. power cord
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 8A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
22575WD	22575WD	2	4.87	13	6





#### Indoor 24HR Mechanical Timer, 1 Polarized Outlet



- 1 Polaried Outlet
- 48 ON/OFF setting, settings repeats daily
- Programmable in 30-minute intervals with LED indicator light
- Convenient finger-grip design allows easy pulling-in and unplugging from the wall
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A/1875W Resistive 10A/1250W Tungsten, 1/2 HP

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50101WD	50101WD	3.87	2.4	1.87	6



## Indoor 24HR Mechanical Timer, 1 Grounded Outlet



- 1 Grounded Outlet
- 96 ON/OFF settings, setting repeat daily
- Programmable in 15 minute intervals
- LED indicator light
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 1/2 HP

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50102WD	50102WD	4.41	2.4	2.64	6



#### Indoor 24HR Mechanical Timer, 1 Grounded Outlet



- 1 Grounded Outlet
- 96 ON/OFF settings, setting repeat daily
- Programmable in 15 minute intervals
- LED indicator light
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 1/2 HP

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50103WD	50103WD	4	2.52	2.3	6

## **INDOOR DIGITAL TIMERS**



#### **Indoor 24HR Digital Timer,** 1 Polarized Outlet



- 1 Polarized Outlet
- Up to 2 ON/OFF settings per day, repeats daily
- Simple-set 4-button programming to the minute
- Large easy-to-read LCD display with slim design that does not block the other receptacle
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 10A 1250W Resistive, 4A 500W Tungsten, 4A Ballast

Model	#	Stock #	Item Details	Length	Width	Height	Case Pack Quantity
50007W	VD	50007WD	1 Pack	2.5	5.12	8.25	6
50027W	VD	50027WD	2 Pack	6.180	4.45	2.48	6



#### **Indoor 7-Day Digital Timer,** 1 Polarized Outlet



- 1 Polarized Outlet
- Program weekday or weekend schedules
- Up to 20 ON/OFF settings, repeats weekly
- Large, easy-to-read LCD display with self recharging battery to save programs
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 10A 1250W Resistive, 4A 500W Tungsten, 4A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50027WD	50027WD	2.52	1.5	1.57	6



#### **Indoor 7-Day Digital Timer,** 1 Polarized Outlet



- 1 Polarized Outlet
- Program weekday or weekend schedules
- Up to 20 ON/OFF settings, repeats weekly
- Large, easy-to-read LCD display with self recharging battery to save programs
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 10A 1250W Resistive, 4A 500W Tungsten, 4A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50008WD	50008WD	2.5	5.25	6.25	6



## **INDOOR DIGITAL TIMERS**



# Indoor 7-Day Heavy Duty Digital Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- 20 ON/OFF settings, repeats weekly
- Program weekday, weekends, or daily schedules
- Countdown, random, and manual modes
- Automatically adjusts at Daylight Savings Time
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 3/4HP, 15A 1875W Resistive, 8A 1000W Tungsten, 8A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50009WD	50009WD	2.5	5.25	8.25	6



# **Indoor 7-Day Astronomical Timer, 2 Grounded Outlets**



- 2 Grounded Outlets
- Program up to 7 ON/OFF settings, repeats weekly 125Vac, 60Hz, 15A 1875W General Pur
- Set weekday, weekend, or daily schedules
- Countdown, random, sunrise/sunset modes
- Automatically adjusts to Daylight Savings Time
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A 1875W General Pur pose/Resistive, 8A 1000W Tungsten, 8A Ballast, 1/2Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50029WD	50029WD	2.5	5	6.75	3



#### Indoor Digital Table Top Timer, 1 Polarized Outlet



- 1 Polarized Outlet
- Up to 2 ON/OFF settings per day, repeats daily
- Simple 4-button programming
- 5ft 18/3 SPT-2 Cord

- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 10A 1250W General/ Resistive, 8.3A Standard Ballast, 8A/1000W Tungsten, 500Va Electronic Ballast, 1/3Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59417WD	59417WD	2.5	7.37	8.25	6

## **INDOOR DIGITAL TIMERS**



#### **Indoor 24HR Flip-Switch Timer**



- Automatically flips the wall switch at programmed times
- Up to 2 ON/OFF settings per day, repeats daily
- Simple 4-button programming easily installs over standard toggle switch
- Fits single or multi-gang wall plate LISTED
- Convenient manual override button and low battery alert
- No wiring required, battery operated

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59744WD	59744WD	2.5	5.25	8	6

## **INDOOR REMOTE TIMERS**

#### **Indoor Wireless Remote, 1 Grounded Outlet**





- 1 Grounded outlet with 1 wireless remote
- Remote works up to 100ft away Light indicator shows power ON/OFF status
- Fast, tool-free stet-up

- Manual power ON/OFF switch
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 15A, 1/2HP, 1875 Resistive, 1250W Tungsten

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59743WD	59743WD	5.5	7.1	1.7	6



#### 3pk Indoor Wireless Remote, 1 Grounded Outlet

- 3 Grounded outlet with 1 wireless remote
- Remote works up to 100ft away
- Light indicator shows power ON/OFF status
- Fast, tool-free set-up

- 2 Polarized outlets

- Manual power ON/OFF switch
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 15A, 1/2HP, 1875 Resistive, 1250W Tungsten

Model #	Stock #	Item Details	Length	Width	Height	Case Pack Quantity
13569WD	13569WD	3 Pack	10	2.25	7	6
59736WD	59736WD	1 Pack	6.73	3.94	1.32	6



#### **Indoor Wireless Remote,** 2 Outlets

- Option to control each outlet seperately
- Wireless remote works up to 50ft away
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/2Hp, 15A/1875W General/

battery included

Resistive, 8A/1000W Tungsten, 500VA

Electronic Ballast, 8.3A Ballast, 12V A23

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59780WD	59780WD	2.5	5.75	7	6

## **INDOOR REMOTE TIMERS**



#### **Indoor Wireless Remote with Wall Switch**



- Turn device ON or OFF with a touch of a button
- Remote switch works up to 80ft away
- Easy to use, push-button ON/OFF control
- Fast, tool-free set-up
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 15A/1800W Resistive, 433.92MHz frequency, CR2032 battery

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59773WD	59773WD	2.5	6	7.5	6



#### **Indoor Wireless Remote with Countdown**



- 1 Polarized Outlet
- Turn plugged-in device ON/OFF with the touch of a button
- Countdown settings include 30min, 1, 2, or 4 hours
- Wireless remote works up to 80ft away
- Indicator light shows ON/OFF status
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 15A/1800W Resistive, 5A/625W Tungsten

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59781WD	59781WD	2.5	5.25	7.25	6

## **OUTDOOR MECHANICAL TIMERS**



# Outdoor 24-Hour Mechanical Timer with Photocell



- 1 Grounded Outlet
- Automatically turns ON at dusk and OFF at dawn or after 2,4,6, or 8 hours, settings repeat daily
- 6 in power cord

- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/2Hp, 10A/1250W Resistive/ General, 8A 1000W Tungsten, 500VA Electronic Ballast, 120Vac 60Hz 8.3A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
2001WD	2001WD	1.75	5.12	7.88	6



# Outdoor 24-Hour Mechanical Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- Up to 24 ON/OFF settings per day, repeat daily
- Programmable in 30 minute intercals
- Weatherproof housing with 6 in power cord
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/2Hp, 15A 1875W Resistive, 8A 1000W Tungsten, 8A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50011WD	50011WD	2.5	6.25	9	6



# Outdoor 24-Hour Heavy Duty Mechanical Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- For heavy duty appliances, controls up to 3/4 HP, 15FLA
- Up to 24 ON/OFF settings per day, repeats daily
- Programmable in 30 minute intercals
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 15A 1875W Resistive, 8A 1000W Tungsten, 8A Ballast, 3/4 Hp, 15FLA, 90LRA

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50012WD	50012WD	3	7.5	9	6

## **OUTDOOR MECHANICAL TIMERS**



# Outdoor 24-Hour Mechanical Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- 96 ON/OFF settings, 15 minuite intervals, settings repeat daily
- 6in 14/3 SJTW cord with mounting holes
- LED indicator light

- Safety covers protect when not in-use
- Manual override switch
- 125V, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 1/2 Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50123WD	50123WD	3.74	2	4.81	6



## Outdoor 24-Hour Heavy Duty Mechanical Timer, 2 Outlets

- LED indicator light
- Safety covers protect when not in-use
- Manual override switch
- 125V, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 3/4 Hp
- 2 Outlets
   2 Grounded Outlets
   3/4 HP rating for heavy duty applications
   96 ON/OFF settings, 15 minute intervals,

settings repeat daily

- 6 in 14/3 SJTW cord with mounting holes

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50124WD	50124WD	3.74	2	4.81	6



#### **Outdoor Dusk to Dawn Lighting Timer**

- 1 or 2 Grounded Outlets
- Automatically turns ON at dusk and OFF at dawn, repeats daily
- 2, 4, 6, or 8 hour countdown option after dusk
- 6 in 14/3 SJTW cord with mounting holes
- LED indicator light
- Safety covers to protect outlets when not in-use
- 125V, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 1/2Hp

Model #	Stock #	Item Details	Length	Width	Height	Case Pack Quantity
50121WD	50121WD	1 Grounded Outlet	2.56	1.81	5.81	6
50122WD	50122WD	2 Grounded Outlet	3.35	1.81	5.81	6



## **OUTDOOR DIGITAL TIMERS**



# Outdoor 24-Hour Digital Light Sensor Timer, 1 Grounded Outlet



- 1 Grounded Outlet
- Automatically turns ON at dusk and OFF at dawn or after 1-9 hours, settings repeat daily
- 6 inch power cord

- 2 Grounded Outlets

- Manual override
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 10A/1250W General Resistive, 8A/1000W tungsten, 500VA Electronic Ballast, 8.3A Ballst, 1/2Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50013WD	50013WD	2.5	6.25	9	6



# Outdoor 7-Day Digital Timer, 2 Grounded Outlets

- Weatherproof housing with 6 inch cord
- Up to 2 ON/OFF settings, repeats weekly
- Option to set daily, weekday, or weekend schedules
- Countdown and random program options with automatic Daylight Savings adjustment
- CFL, LED, and incandescent compatible
- CFL, LED, and incandescent compatible 125V 60Hz 15A /1875W Posistivo
- 125V, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 8A Ballast, 1/2 Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50014WD	50014WD	2.5	6.25	9	6



# Outdoor 7-Day Heavy Duty Digital Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- Up to 2 ON/OFF settings, repeats weekly
- Programmable to the minute
- Self-charging battery stores programs
- Weatherproof housing with 12 in cord
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 15A/1875W Resistive, 15A/1000W Tungsten, 8A Ballast, 3/4 Hp, 15FLA, 90LRA

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50015WD	50014WD	2.5	6.25	9	6

## **OUTDOOR DIGITAL TIMERS**



# Outdoor 24 Hour Digital Block Heater Timer, 2 Grounded Outlets



- 2 Grounded Outlets
- 1 ON/OFF settings per day, repeats daily
- Easy 2-button programming
- 6 inch power cord

- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 8A Ballast, 1/2 Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50016WD	50016WD	2.5	6.25	9	6



#### **Outdoor Wireless Remote, 1 Grounded Outlet**



- 1 Grounded Outlet
- Remote Works up to 100ft away
- Weatherproof housing with 6 inch 16/3 SJTW power cord
- 12 Volt battery included
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 8A/1000W Resistive, 5A/625W Tungsten, 12V A23 battery included

Model #	Stock #	Length	Width	Height	Case Pack Quantity
32555WD	32555WD	2	6	9.5	6



# Outdoor 24 Hour Photocell Timer and Remote, 3 Grounded Outlets



- 3 Grounded Outlets
- Turns plugged-in devices ON at dusk and OFF after 2,4,6, or 8 hours, or OFF at dawn
- Operate up to 3 different plugged-in devices using one remote
- Wireless remote works up to 80ft
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/2Hp, 10A/1250W General/ Resistive, 8A/1000W Tungsten, 500VA Electronic Ballast, 120Vac 60Hz 8.3A Ballast, 12V A23 Battery

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59746WD	59746WD	1.75	7	10.25	6



## **OUTDOOR DIGITAL TIMERS**



# Outdoor Wireless Remote, 3 Grounded Remote



- 3 Grounded Outlets
- Wireless remote works up to 50ft
- Fast, tool-free stet up
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/3Hp, 13A/1625W General/ Resistive, 8A/1000W Tungsten, 500VA Electronic Ballast, 120Vac 60Hz 8.3A Ballast, 12V A23 Battery

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59748WD	59748WD	7.5	6.5	11	3



#### **Outdoor Remote Control, 1 Grounded Outlet**



- 1 Grounded Outlet
- 6 inch 14/3 SJTW cord with angled plug does not block the 2nd outdoor wall outlet
- 2 Mounting holes for improving stability
- Manual override button with LED indicator light
- Programmable remote works up to 100ft away
- 125Vac, 60Hz, 15A/1875W Resistive, 10A/1250W Tungsten, 1/2Hp

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50125WD	50125WD	2.63	1.5	5.19	6



# Outdoor Remote Control with Photocell, 3 Grounded Outlets



- 3 grounded outlet
- 6 inch 14/3 SJTW cord with angled plug does not block the 2nd outdoor wall outlet
- 2 Mounting holes for improving stability
- Manual override button with LED indicator light
- Programmable remote works up to 100ft away
- 125Vac, 60Hz, 15A/1875W Resistive, 10A/ 1250W Tungesten, 1/2Hp
- Automatically turns ON at dusk and OFF at dawn, repeats daily
- 2,4,6, or 8-hour countdown options after dusk

Model #	Stock #	Length	Width	Height	Case Pack Quantity
50126WD	50126WD	3.88	1.5	6	6

## YARD STAKES



# Outdoor Yard Stake with Photocell and Built-In Timer, 6 Grounded Outlets



- 6 Grounded Outlets
- Automatically turns ON at dusk and OFF at dawn, or after 2,4,6, or 8 hours, repeats daily
- 6ft 16/3 SJTW cord

- Safety covers
- CFL compatible
- 13A, 125V, 60Hz, 1625W

Model #	Stock #	Length	Width	Height	Case Pack Quantity
13547WD	13547WD	3.75	6.5	10	6



# Outdoor Yard Stakes with Photocell and Built-In Timer, 3 Grounded Outlets

- Safety covers
- CFL compatible
- 10A, 125V, 60Hz, 1250W
- Automatically turns ON at dusk and OFF at dawn, or after 2,4,6, or 8 hours, repeats daily
- 6ft 16/3 SJTW cord

- 6 Grounded Outlets

Model #	Stock #	Length	Width	Height	Case Pack Quantity
17321WD	17321WD	4.125	5.75	9	6



# Outdoor Yard Stake with Photocell and Remote Control, 6 Grounded Outlets

ets c CLISTED

- 6 Grounded Outlets
- 6ft 14/3 SJTW cord
- Automatically turns ON and dusk and OFF after 2,4,6, or 8hr or at dawn, or remote ON/OFF
- Optional dusk ON dawn OFF setting on remote control
- CFL, LED, incandescent compatible
- 125V, 13A, 1625W

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59785WD	59785WD	4.25	5.25	9	6



## **IN-WALL MECHANICAL TIMERS**



#### **In-Wall 15 Minute Spring Wound Timer**



- Automatically turns OFF after selected time
- Turn dial to select ON time, up to 15 minutes
- Easy to install in place of existing wall switch
- Lowers energy costs

- Fits decorator or standard switch plates
- 125V, 60Hz, 20A 2500W Resistive, 8A
   1000W Tungsten, 5A 625Va Ballast, 15FLA
   90LRA, SPST

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59711WD	59711WD	White	2.12	3	5.87	3
59712WD	59712WD	Light Almond	2.12	3	5.87	3
59713WD	59713WD	Gray	2.12	3	5.87	3
59714WD	59714WD	White and Light Almond	2.12	3	5.87	3



#### **In-Wall 30 Minute Spring Wound Timer**



- Automatically turns OFF after selected time
- Turn dial to select ON time, up to 30 minutes
- Easy to install in place of existing wall switch
- Lowers energy costs

- Fits decorator or standard switch plates
- 125V, 60Hz, 20A 2500W Resistive, 8A 1000W Tungsten, 5A 625Va Ballast, 15FLA 90LRA, SPST

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59714WD	59714WD	White	2.125	3	5.87	6
59715WD	59715WD	Light Almond	2.125	3	5.87	6
59716WD	59716WD	Gray	2.125	3	5.87	6

## **IN-WALL MECHANICAL TIMERS**



#### **In-Wall 60 Minute Spring Wound Timer**

- Automatically turns OFF after selected time
- Easy to install in place of existing wall switch
- Lowers energy costs

- Fits decorator or standard switch plates
- Turn dial to select ON time, up to 60 minutes 125V, 60Hz, 20A 2500W Resistive, 8A 1000W Tungsten, 5A 625Va Ballast, 15FLA 90LRA, SPST

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59717WD	59717WD	White	2.12	3	5.87	6
59718WD	59718WD	Light Almond	2.12	3	5.87	6
59719WD	59719WD	Gray	2.12	3	5.87	6
59723WD	59723WD	White and Light Almond	2.12	3	5.87	6



#### In-Wall 24 hour Mechanical Timer



- Up to 24 ON/OFF settings per day, repeats daily
- Programmable in 30 minnute intervals
- Never lose pins cannot be removed or lost
- Convenient override switch

- Fits into a single or multi-gang switch box
- CFL Compatible
- 125Vac, 60Hz, 1Hp, 20A 2500W Resistive, 8A 1000W Tungsten, 8A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59745WD	59745WD	2.25	4.25	8.25	6

## **IN-WALL DIGITAL TIMERS**



#### **In-Wall 30 Minute Digital Countdown Timer**



- Automatically turns OFF after selected time
- 5 settings OFF after 5,10,15,or 30 minutes, or OFF
- Fits any single or multi-gang decorator switch plate
- Easily installs in place of existing wall switch
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 1/4Hp, 15A 1800W
   General/ Resistive, 8.3A 1000W Tungsten, 8.3A 1000VA Ballast

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59007WD	59007WD	White	2.12	3	6	6
59720WD	59720WD	Light Almond	2.12	3	6	6



#### **In-Wall 60 Minute Digital Countdown Timer**



- Automatically turns OFF after selected time
- 5 settings OFF after 5,10,15,or 30 minutes, or 60 minutes, or OFF
- Fits any single or multi-gang decorator switch plate
- Easily installs in place of existing wall switch
- CFL, LED, and incandescent compatible
- 120V, 60Hz, 1/4Hp, 15A 1800W General/ Resistive, 8.3A 1000W Tungsten, 8.3A 1000VA Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59008WD	59008WD	2.12	3	6	6



#### **In-Wall 8 Hour Digital Countdown Timer**



- Automatically turns OFF after selected time
- 5 countdown settings 1,2,4, or 8 hours and off
- Easily installs in place of existing wall switch
- Fits any single or multi-gang decorator switch plate
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 1/4Hp, 15A/1800W General/Resistive, 8.3A/1000W Tungsten, 8.3A/1000VA Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59013WD	59013WD	2.12	3	6	6

## **IN-WALL DIGITAL TIMERS**



#### **In-Wall 12 Hour Digital Countdown Timer**



- Automatically turns OFF after selected time CFL, LED, and incandescent compatible
- 5 countdown settings 2, 4, 8, or 12 hours
- Easily installs in place of existing wall switch
- Fits any single or multi-gang decorator switch plate
- 120V, 60Hz, 1/4Hp, 15A/1800W General/ Resistive, 8.3A 1000W Tungsten, 8.3A 1000VA Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59014WD	59014WD	2.12	3	5.87	6



#### **In-Wall 4 Hour Digital Countdown Timer**



- Automatically turns OFF after selected time
- 5 countdown settings OFF after 5, 10, 15, 20, or 30 minutes or 1, 2, 4 hours
- Easily installs in place of existing wall switch
- Fits any single or multi-gang decorator switch plate
- CFL, LED, and incandescent compatible
- 125Vac, 60Hz, 1/2Hp, 15A General/Resistive, 1000W Tungsten, 500VA Electronic Ballast, 8.3A Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59724WD	59724WD	2.25	4.25	8.12	6



## **IN-WALL PROGRAMMABLE TIMERS**



#### **In-Wall 7-Day Digital Timer**



- Up to 7 ON/OFF settings per day, repeats weekly
- May be ganged with other switches
- Simple push button programming with self recharging battery to store programs
- Simple push button setting

- Self recharging battery stores programs
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/4Hp, 15A General/Resistive, 1000W Tungsten, 1000VA Ballast

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59018WD	59018WD	White	2	4.25	8.25	6
59028WD	59018WD	Light Almond	2	4.25	8.25	6



#### **In-Wall 7-Day Astronomical Digital Timer**



- Up to 7 ON/OFF settings per day, repeats weekly
- Option to program daily, weekday, or weekend schedule
- Astronomica features

- Fits single or multi-gang decorative wall plates
- CFL, LED, and incandescent compatible
- 125V, 60Hz, 1/4Hp, 15A General/Resistive, 1000W Tungsten, 1000VA Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59019WD	59019WD	2	5	6.75	6



#### **In-Wall 7-Day Digital Timer (No Neutral)**



- Up to 18 ON/OFF settings, repeats weekly
- Programmable to the minute
- No neutral wire required for easy installation and self-recharging battery stores program
- May be ganged with other switches
- CFL, LED, incandescent compatible
- 125V, 60Hz, 1/4Hp, 6.4A Resistive, 800W Tungsten, 800VA Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59020WD	59020WD	2	4.25	8.25	6



# Indoor Dusk to Dawn Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Easy installatioin with screw-in design
- Works with incandescent, halogen, CFL, LED bulbs
- Time delay eliminates flicker and false ON/ OFF triggers
- 120Vac 60Hz, 150W Tungsten, 150W Magnetic Ballast, 05A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59404WD	59404WD	1.67	4.12	6.62	6



# Outdoor Dusk to Dawn Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Flexible spring-loaded contact allows precise sensor orientation
- Easy installation with screw-in design
- Works with incandescent, halogen, CFL, LED bulbs
- 120Vac 60Hz, 150W Tungsten, 150W Magnetic Ballast, 05A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59405WD	59405WD	1.75	4.12	6.62	6



# Outdoor Dusk to Dawn Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Flexible spring-loaded contact allows precise sensor orientation
- Easy installation with screw-in design
- Works with incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- Time delay eliminates flicker and false ON/ OFF triggers
- 120Vac 60Hz, 150W Tungsten, 150W Magnetic Ballast, 05A Electronic Ballast

Model #	Stock #	Product Color	Length	Width	Height	Case Pack Quantity
59447WD	59447WD	Black	4.12	6.63	6.62	6



# Outdoor Dusk to Dawn Floodlight Control with Photocell Socket





- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Flexible spring-loaded contact allows precsise sensor orientation
- Designed for use with PAR bulbs

- Easy installation with screw-in design
- Time delay eliminates flicker and false ON/ OFF triggers
- Works with incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz, 150W Tungsten, 150W Magnetic Ballast, 0.5A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
1472WD	1472WD	2.75	4.12	6.62	6



# Indoor Dusk to Dawn Smart Light Control with Timer



- Program lights to turn ON at dusk and OFF after 2, 4, 6, or 8 hours or at dawn
- Random setting to deter crime
- Wireless remote controls works up to 80ft away
- Fast, tool-free installation no wiring required
- CFL, LED, incandescent compatible
- 120V, 60Hz, 60W Max

Model #	Stock #	Product Title	Length	Width	Height	Case Pack Quantity
59406WD	59406WD	Indoor Dusk to Dawn Smart Light Control with Photocell Timer	1.75	3.88	6.56	6
59415WD	59415WD	Indoor Dusk to Dawn Smart Light Control with Photocell Timer with Remote	1.75	5	6.63	4



#### **Indoor Light Control with Photocell Timer**



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Fast, tool-free installation

- Works with incandescent, halogen, CFL LED bulbs
- Time delay eliminates flicker and false ON/ OFF triggers
- 125V, 60Hz, 400W Max

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59405WD	59405WD	1.75	4.12	6.62	6

#### **Outdoor Twistlock Light Control WITH Photocell**





- OFF at dawn
- Requires no seasonal adjustment, photocell activates with abscence of natural sunlight
- 120Vac with surge protection

- NEMA loicking-type plug configuration
- High pressure sodium twist lock, metal halide
- 120Vac 60Hz, 1800W Tungsten, 1100VA Magnetic Ballast, 5A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
L4700WD	L4700WD	2.28	4.12	6.62	12



# Outdoor Heavy Duty - Twistlock Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Heavy duty 110-227Vac with surge protection
- NEMA loicking-type plug configuration
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium, metal halide
- 110-277Vac 60Hz, 1800W Tungsten, 1000VA Magnetic Ballast, 5A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59412WD	59412WD	2.62	4.12	6.62	6





# Outdoor Dusk to Dawn Hardwired Post Eye Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Time delay eliminates flicker and false ON/OFF triggers
- Heavy duty theraml bi-metal switch
- Fits 11/16inch diameter hole
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 5A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59408WD	59408WD	1.25	4.12	6.62	6



# Outdoor Hardwired Post Eye Light Control with Photocell and Wall Plate



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Fits standard outlet box
- Includes weatherproof wall plate with neoprene gasket, nut, and washer gasket
- Time delay eliminates flicker and false ON/ OFF triggers
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 5A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59409WD	59409WD	2.25	4.12	6.62	6



# **Outdoor Dusk to Dawn Swivel Mount Light Control**



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Time delay eliminates flicker and false ON/OFF triggers
- Includes light level slide adjustment
- 1/2" NPT or 3/4" knockout
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 3A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59413WD	59413WD	1.25	4	6.62	6



# Outdoor Dusk to Dawn Hardwired Stem Mount Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Time delay eliminates flicker and false ON/OFF triggers
- Includes light level slide adjustment
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 3A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity	
59410WD	59410WD	1.25	4.12	6.62	6	





#### **360 Motion Activated Light Control**

Woods 360 Motion Activated Light Control is perfect for laundry room, garage, basement or attic. It automatically turns the light on when motion is detected. It senses activity at distances of up to 20 ft.

- Automatically turns light OFF five (5) minutes after motion stops
- Rated for indoor use only
- Works with LED, CFL, and incandescent bulbs
- Ratings: 120VAC, 60Hz, 75-Watt Max
- Ratings: Perfect for laundry room, garage, basement or attic

Model #	Stock #	Length	Width Height		Case Pack Quantity
50065	50065	2.76	3.87	7.2	6



#### Outdoor Dusk to Dawn Hardwired Stem and Swivel Light Control with Photocell



- Automatically turns light ON at dusk and OFF at dawn
- Requires no seasonal adjustment, photocell activates with absence of natural sunlight
- Time delay eliminates flicker and false ON/OFF triggers
- Stem and swivel mount allows adjustable placement
- Includes light level slide adjustment
- Mounts through a standard 1/2" NPT or 3/4" knockout
- Works with Incandescent, halogen, CFL, LED, mercury vapor, high pressure sodium
- 120Vac 60Hz 1800W Tungsten, 1100VA Magnetic Ballast, 15A Electronic Ballast

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59411WD	59411WD	1.5	4.12	6.62	6

## TIMER SWITCHES



#### **Indoor 24hr Heavy Duty Mechanical Time** Switch, 120V/40A SPST



- Up to 24 ON/OFF settings per day, repeats daily
- Industrial-grade lockable metal box with 1/2 inch and 3/4 inch knockouts
- Heavy duty gear train with pins that cannot be removed
- Manual override switch
- 120Vac, 60Hz, SPST, 40A General/Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 2Hp (24FLA)

Model #	Stock #	Item Details	Length	Width	Height	Case Pack Quantity
59101WD	59101WD	Indoor	3.87	5.37	8.37	2
59101MWD	59101MWD	Indoor/Outdoor	3.87	5.37	8.37	2
59101RWD	59101RWD	Outdoor	3.87	5.37	8.37	2



#### **Indoor 24hr Heavy Duty Mechanical Time** Switch, 120V/40A DPST



- Up to 24 ON/OFF settings per day, repeats daily
- Industrial-grade lockable metal box with 1/2 inch and 3/4 inch knockouts
- Heavy duty gear train with pins that cannot be removed
- Manual override switch
- 120Vac, 60Hz, DPST, 40A General/Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 2Hp (24FLA)

Model #	Stock #	Length	Width	Height	Case Pack Quantity
59103WD	59103WD	3.87	5.37	8.37	2

## **TIMER SWITCHES**



# Indoor 24hr Heavy Duty Mechanical Time Switch, 208-277V/40A DPST



- Up to 24 ON/OFF settings per day, repeats daily
- Industrial-grade lockable metal box with 1/2 inch and 3/4 inch knockouts
- Heavy duty gear train with pins that cannot be removed
- Manual override switch
- 208-277Vac, 50Hz, DPST, 40A General/ Resistive, 40A Tungsten, 20A Ballast, 1000VA Pilot Duty, 5Hp (28 FLA)

Model #	Stock #	Item Details	Length	Width	Height	Case Pack Quantity
59104WD	59104WD	Indoor	3.87	5.37	8.37	2
59104RWD	59104RWD	Outdoor	3.87	5.37	8.37	2
59104MWD	59104MWD	Indoor/Outdoor	3.87	5.37	8.37	2

## **OUTDOOR EXTENSION CORDS**


#### Woods outdoor extension cords are perfect for a variety of outdoor applications.

- 125 Voltage Rating
- Common Applications: Electric Push Mower, Hedge Trimmer, Electric Drill



530

#### **Standard Extension Cords**





9940010



547860

<sup>\*\*</sup>Product packaging is advertised in Meters



<sup>\*</sup>Black Plug

Bonus Carry Strap included

## **OUTDOOR EXTENSION CORDS**



#### **Standard Outdoor Tritap Extension Cords**

**Specifications** 

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
825	14/3	SJTW	25′	7.6 m	Orange	15	12
826	14/3	SJTW	50′	15.2 m	Orange	15	6
827	14/3	SJTW	100′	30.5 m	Orange	13	12
990824	12/3	STW	2'	0.6 m	Orange	15	4
819	12/3	SJTW	50′	15.2 m	Orange	15	3
820	12/3	SJTW	100′	30.5 m	Orange	15	2

#### **Standard 3-Outlet Extension Cords**



Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
40038803	16/3	SJTW	3'	0.9 m	Orange	13	24
2864	16/3	SJTW	9′	9′ 2.7 m		13	12
540650 * **	16/3	SJTW	10′	3 m	Orange	13	14
545454 * **	16/3	SJTW	15′	4.6 m	Orange	13	21
545502* **	16/3	SJTW	30′	9.1 m	Orange	13	12
545528* **	16/3	SJTW	50′	15.2 m	Orange	13	10
872	14/3	SJTW	9′	2.7 m	Orange	15	4

<sup>\*</sup>Black Plug \*\*Product packaging is advertised in Meters

<sup>\*</sup>Black Plug \*\*Product packaging is advertised in Meters

## **SPECIALTY EXTENSION CORDS**

#### Woods has a variety of specialty extension cords to meet a variety of indoor and outdoor needs.

#### **Garage & Workshop Extension Cords**

Woods garage and workshop extension cords are tough enough to stand up to temperature changes, dirt and abrasion.

- Temperature rating of -40°F to 167°F (-40°C to 75°C).
- 125 Voltage Rating
- Common Applications: Air Compressor, Chop Saw, Electric Chain Saw

#### **Specifications**

ı	Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
	258	16/2	SJTW	15′	4.6 m	Black	13	15
	260	16/3	SJTW	8′	2.4 m	Black	13	15
9	990261	16/3	SJTW	15′	4.6 m	Black	13	4

#### **Garage & Workshop 3-Outlet Extension Cord**

#### **Specifications**

Pai	rt #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
3522	27408	14/3	SJTW	15′	4.6 m	Black	15	12

#### Push-Lock Extension Cords w/ Black Plug

Woods® push-lock extension cords keep your tools plugged in while doing common yard work.

- Temperature rating of -40°F to 167°F (-40°C to 75°C).
- 125 Voltage Rating
- Common Applications: Electric Push Mower, Leaf Blower, Hedge Trimmer

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
54327201**	16/2	SJTW	100′	30.5 m	Lime Green	10	3
54157902**	14/3	SJTW	30′	9.1 m	Red	15	13
54158502**	12/3	SJTW	100′	30.5 m	Yellow	15	13

<sup>\*\*</sup>Product packaging is advertised in Meters



990261



35227408



54157902



## **INDOOR EXTENSION CORDS**



359W



## Woods indoor extension cords bring power where you need it.

- Temperature rating of -4°F to 167°F (-20°C to 75°C)
- 125 Voltage Rating
- Common Applications: Lamp, Fan, Indoor Holiday Lighting

#### **3-Outlet Extension Cords**

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
600	16/2	SPT-2	6′	1.8 m	Brown	13	25
600W	16/2	SPT-2	6′	1.8 m	White	13	25
647760**	16/2	SPT-2	6′	1.8 m	Black	13	25
292	16/2	HPN	6′	1.8 m	Black	15	10
601	16/2	SPT-2	9′	2.7 m	Brown	13	25
601W	16/2	SPT-2	9′	2.7 m	White	13	25
602	16/2	SPT-2	12'	3.7 m	Brown	13	24
602W	16/2	SPT-2	12'	3.7 m	White	13	24
603	16/2	SPT-2	15′	4.6 m	Brown	13	9
603W	16/2	SPT-2	15′	4.6 m	White	13	9
359W*	16/2	SPT-2	15′	4.6 m	White	10	9
94158901	16/2	SPT-2	20′	6.1 m	White	13	24
608	16/3	SPT-2	8′	2.4 m	Brown	13	10
609	16/3	SPT-2	8′	2.4 m	White	13	10
2611	16/3	SPT-2	8′	2.4 m	Black	13	10

<sup>\*</sup>with switch

<sup>\*\*</sup>Product packaging is advertised in Meters

# **INDOOR EXTENSION CORDS**





#### **Holiday Indoor Extension Cords**

Woods® holiday extension cords come in dark green and white colors to blend with holiday decorations.

- Temperature rating of -4°F to 167°F (-20°C to 75°C)
- 125 Voltage Rating
- Common Applications: Holiday Wreaths, String Lights, Tree Décor

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m) Color		Amps	Case Pack Quantity
32189^	18/2	SPT-2	12'	3.7 m	Green	5	25
2188^	18/2	SPT-2	15′	4.6 m	White	5	25
2189^	18/2	SPT-2	15′	4.6 m	Green	5	25
10203*	18/2	SPT-2	15′	4.6 m	Green	5	12
12600G	16/2	SPT-2	6′	1.8 m	Green	13	25
548290* **	16/2	SPT-2	10′	3 m	White	13	8

<sup>\*</sup>with Foot Switch

<sup>^</sup>Multi-Outlet With Switch

<sup>\*\*</sup>Product packaging is advertised in Meters

# **INDOOR SPECIALTY CORDS**



540038



542703

Woods indoor specialty extension cords provide power options for a variety of specific indoor applications.

#### **Office Extension Cords**

- Temperature rating of:
  - o SPT-2 and SVT -4°F to 167°F (-20°C to 75°C)
  - o SJTW -40°F to 167°F (-40°C to 75°C)
  - o SPT-3 -4°F to 140°F (-20°C to 60°C)
- 125 Voltage Rating
- Common Applications: Computer, Printer, Copier

#### **Specifications**

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Cord Color	Amps	Case Pack Quantity
540038**	16/2	SPT-2	6′	1.8 m	Gray	13	25
990547*	16/2	SVT	20′	6.1 m	Gray	13	6
6991	16/3	SPT-2	8" x 3	0.2 m	Multi	13	3
814	16/3	SPT-2	3′	0.9 m	Orange	13	12
542652**	16/3	SPT-2	10′	3 m	Beige	13	18
2865	16/3	SJTW	10′	3 m	Beige	13	8
542654**	16/3	SPT-3	15′	4.6 m	White	13	28
2867	16/3	SJTW	20′	6.1 m	Gray	13	12
5601*	16/3	SJTW	25′	7.6 m	Black	13	12
545517**	16/3	SJTW	30′	9.1 m	Black	13	12
863	14/3	SPT-3	3′	0.9 m	Yellow	15	12
537901**	14/3	SPT-3	6′	1.8 m	Gray	15	36
542703**	14/3	SPT-3	9′	2.7 m	Gray	15	28
542705**	14/3	SPT-3	14′	4.3 m	Gray	15	20

<sup>\*</sup>Single Outlet

<sup>\*\*</sup>Product packaging is advertised in Meters

### **ADAPTER**



542660

### **Indoor Major Appliance Cords**

- Temperature rating of -4°F to 140°F (-20°C to 60°C)
- 125 Voltage Rating
- Common Applications: Air Conditioner, Space Heater, Refrigerator

#### **Specifications**

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Color	Amps	Case Pack Quantity
542660**	14/3	SPT-3	6′	2.0 m	Gray	15	36
542673**	14/3	SPT-3	9′	3.0 m	Gray	15	28

<sup>\*\*</sup>Product packaging is advertised in Meters

### **Small Appliance Replacement Cords**

- Temperature rating of -4°F to 167°F (-20°C to 75°C)
- 125 Voltage Rating
- Common Applications: Coffee Maker, Waffle Iron, Indoor Grill

### **Specifications**

Part #	Gauge/ Conductors	Wire Type	Length (ft)	Length (m)	Color	Amps	Case Pack Quantity
293	18/2	HPN	2'	0.6 m	Black	10	10
291	18/2	HPN	6′	1.8 m	Black	10	10
290	16/2	HPN	6′	1.8 m	Black	15	10





548303

### Woods Gas Range Adapter offers a safe way to convert electric ranges for gas use.

#### **Specifications**

Part #	Color	Amps	Case Pack Quantity	NEMA Plug	NEMA Receptacle
548303	White	15	6	14-50P	5-15R

### **CORD ORGANIZATION**

Woods® cord organization offers options for keeping bulky extension cords, ropes, and holiday lighting tangle-free.

\*Product images displayed on following page

#### **Accessories**

**Specifications** 

Part #	Description	Color	Case Pack Quantity
272802	Carry Strap	Black	6

### **Cord Storage Wraps**

**Specifications** 

Part #	Holds	Color	Case Pack Quantity
2803	100' of 16/3 Gauge Cord	Black	12
E101	150' of 16/3 Gauge Cord	Yellow	24

#### **Cord Storage Reels**

**Specifications** 

Part #	Holds	Color	Case Pack Quantity
547702**	.7702** 150' of 16/3 Gauge Cord Black		8
E102	125' of 14/3 Gauge Cord	Red/Black	8
E103^	125' of 14/3 Gauge Cord	Red/Black	4
22849*	100' of 14/3 Gauge Cord	Black	6

<sup>\*</sup>with Metal Stand

#### **Cord Reels**

**Specifications** 

Part #	Gauge/ Conductor	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
2801	16/3	SJTW	Yellow/Black	25′	7.6 m	4	13	3
4907	16/3	SJTW	Black/Yellow	25′	7.6 m	4	13	4

<sup>\*</sup>with Metal Stand

### Retractable Cord Reel w/ Black Banana Plug

**Specifications** 

Part #	Cord	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
E315	16/3	SJTW	Yellow/Black	20′	6 m	3	13	4

### Retractable Cord Reel w/ Work Light

**Specifications** 

Part #	Cord	Wire Type	Color	Length (ft)	Length (m)	Outlets	Amps	Case Pack Quantity
E216	16/3	SJTW	Yellow/Black	20′	6 m	1	13	4

<sup>^</sup>with Stand

<sup>\*\*</sup>Product packaging is advertised in Meters

<sup>\*\*</sup>Product packaging is advertised in Meters

# **WALL TAPS**



### **Wall Adapter**

- Charging cradle
- Easy pull design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41013	078693410130	3-Outlet Wall Adapter	White	3	0	0	0	15A 120VAC 60Hz 1800W	12
41196	078693411960	6-Outlet Wall Adapter	White	6	0	0	0	15A 120VAC 60Hz 1800W	12



### **Space Saver 6-Outlet Wall Adapter**

- 6 side entry outlets
- Charging cradle
- Safety covers
- Easy pull design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41261	078693412615	Space Saver 6-Outlet Wall Adapter	White	6	0	0	0	15A 125VAC 60 Hz 1875W	6





### 2-Outlet Wall Adapter with 2 USB-A

- 2 USB ports
- 2 Grounded Outlets
- Fold out cord wrap
- Phone charging cradle
- 2.4 Amps

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41230	078693412301	2-Outlet Wall Adapter with 2 USB-A	White	2	2 USB-A	2.4A	0	15A 120VAC 60Hz 1800W	6



# **WALL TAPS**





### 1-Outlet Wall Adapter with 4 USB

- 4 USB ports
- 1 Grounded Outlet
- Fold out cord wrap
- Phone charging cradle
- 3.4 Amp

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41233	078693412332	1-Outlet Wall Adapter with 4 USB-A	White	1	1 USB-A	3.4A	0	15A 125VAC 60 Hz 1875W	6





### 1 Outlet Slim Wall Tap

- 1 Grounded Outlets
- 1 USB-A port
- 3.1 Amps
- 1 USB-C Fast Charging port
- Slim design, won't block second outlet

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in ft)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41289	078693412899	1 Outlet Slim Wall Tap	White	1	1 USB-A 1 USB-C	3.1A	0	0	15A 125VAC 60Hz 1875W	6





### 2 Outlet Slim Wall Tap 2 USB with 10W Qi Charging

- 2 Grounded Outlets
- 2 USB-A Port
- 2.4 Amps
- 10W Qi Charging
- Wireless charging
- Wall-mountable

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in ft)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41288	078693412882	2 Outlet Wall Tap with 10W Qi Charging	White	2	2 USB-A	2.4A	0	0	15A 125VAC 60Hz 1875W	6

# **WALL TAPS**







### **3 OUTLET USB FAST CHARGING POWER TAP**

- 3 Grounded Outlets
- 3 USB-A port
- 5.4 Amps
- 1 USB-C Fast Charging port
- Phone Shelf

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in ft)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41286	078693412868	3 Outlet USB Fast Charging	White	3	3 USB-A 1 USB-C	5.4A	0	0	15A 125VAC 60Hz 1875W	6



### **6-OUTLET SURGE TAP, 280 JOULES**

- Phone cradle
- Easy pull design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41197	078693411977	6-Outlet Surge Tap, 280 Joules	White	6	0	0	280 Joules	15A 120VAC 60Hz 1800W	12
41076	078693410765	6-Outlet Surge Tap, 1440 Joules	White	6	0	0	1440 Joules	15A 120VAC 60Hz 1800W	6



### 1-OUTLET APPLIANCE SURGE TAP, 1080 JOULES

- End of protection alarm
- LED indicator
- 1080 Joules
- Appliance protection

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41008	078693410086	1-Outlet Appliance Surge Tap, 1080 Joules	White	1	0	0	1080 Joules	15A 120VAC 60Hz 1800W	6



### **3-OUTLET SURGE TAP, 1000 JOULES**

- Phone cradle
- Overload protection
- Safety covers
- Easy pull design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41034	078693410345	3-Outlet Surge Tap, 1000 Joules	White	3	0	0	1000 Joules	15A 120VAC 60Hz 1800W	6





### **3-OUTLET SURGE TAP, 560 JOULES, 2 USB-A**

- 2.4 Amps USB
- Phone cradle
- LED indicator
- Safety covers
- Easy pull design
- 2 USB Type-A ports

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41029	078693410291	3-Outlet Surge Tap, 560 Joules, 2 USB-A	White	3	2 USB-A	2.4A	560 Joules	15A 120VAC 60Hz 1800W	6







### **3-OUTLET SURGE TAP, 560 JOULES, 2 USB**

- 2.4 Amps USB
- Phone cradle
- LED indicator
- Safety covers
- Easy pull design
- 1 USB Type-A port & 1 USB Type-C port

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41030	078693410307	3-Outlet Surge Tap, 560 Joules, 2 USB	White	3	1 USB-A 1 USB-C	2.4A	560 Joules	15A 120VAC 60Hz 1800W	6





### 6-OUTLET SURGE TAP, 1000 JOULES, 2 USB-A

- 2.4 Amps USB
- Phone cradle
- LED indicator
- Safety covers
- Easy pull design
- 2 USB Type-A ports

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41079	078693410796	6-Outlet Surge Tap, 1000 Joules, 2 USB	White	6	2 USB-A	2.4A	1000 Joules	15A 120VAC 60Hz 1800W	6









### 6-OUTLET SURGE TAP, 1000 JOULES, 2 USB

- 2.4 Amps USp
- Phone cradle
- LED indicator
- Safety covers

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41080	078693410802	6-Outlet Surge Tap, 1000 Joules, 2 USB	White	6	1 USB-A 1 USB-C	2.4A	1000 Joules	15A 120VAC 60Hz 1800W	6







# SPACE SAVER 3-OUTLET SURGE TAP, 1060 JOULES, 4 USB

- 4 USB ports
- 2.4 Amps
- Side entry
- Phone cradle

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41260	078693412608	Space Saver 3-Outlet Surge Tap, 1060 Joules, 4 USB	White	3	3 USB-A 1 USB-C	2.4A	1060 Joules	15A 120VAC 60Hz 1800W	6



### **6-OUTLET SWIVEL SURGE TAP, 1440 JOULES**

- Space saving
- LED indicators
- 3-outlets rotate  $90^{\circ}$
- EMI/RFI noise filter

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41424	078693414244	6-Outlet Swivel Surge Tap, 500 Joules, 2 USB	White	6	2 USB-A	2.4A	500 Joules	15A 120VAC 60Hz 1800W	6
41423	078693414237	6-Outlet Swivel Surge Tap, 1440 Joules	White	6	0	0	1440 Joules	15A 120VAC 60Hz 1800W	6





### 6-OUTLETS WALL TAP WITH USB-C, 3.1 AMPS 20W PD FAST CHARGING 1200J

- 6 grounded outlets

- 1 USB-C Fast Charging port

- 1 USB-A port

- 2100 Joules of Surge Protection

- 3.1 Amps

- 20W PD fast charging

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41287	078693412875	6 Outlet PD Fast Charging Surge Tap	White	6	1 USB-A 1 USB-C	3.1 A	0	2100 Joules	15A 125VAC 60Hz 1875W	6





### **3 OUTLET SURGE TAP WITH NIGHLIGHT**

- 3 grounded outlets

- 1 USB-C Fast Charging port

- 1 USB-A port

- 900 Joules of Surge Protection

- 3.1 Amps

- Night light

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41279	078693412790	3 Outlet Surge Tap with Nightlight	White	3	1 USB-A 1 USB-C	3.1 A	0	900 Joules	15A 125VAC 60Hz 1875W	6

# **POWER STRIPS**



### 4-Outlet Power Strip with 1.5' Cord

- Safety covers
- 1.5' cord

Iter Num	LIPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
4129	9 078693412998	4-Outlet Power Strip with 1.5' Cord	White	4	0	0	1.5	15A 125VAC 60Hz 1875W	12



### **6-Outlet Power Strip**

- Overload protection

- 4' cord

- 2' cord

- 6' cord

- 2.5' cord

- 8' cord

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
41366	078693413667	6-Outlet Power Strip with 2' Cord	White	6	0	0	2	15A 120VAC 60Hz 1800W	12
41367	078693413674	6-Outlet Power Strip with 4' Cord	White	6	0	0	4	15A 120VAC 60Hz 1800W	6
41435	078693414350	2-Pack 6-Outlet Power Strip with 2.5' Cord	White	6	0	0	2.5	15A 120VAC 60Hz 1800W	6
41434	078693414343	6-Outlet Power Strip with 6' Cord	White	6	0	0	6	15A 120VAC 60Hz 1800W	6
41436	078693414367	6-Outlet Power Strip with 8' Cord	White	6	0	0	8	15A 120VAC 60Hz 1800W	6

### **POWER STRIPS**



### 6-Outlet Corner Power Strip with 6' Cord

- Cord tucks into housing
- 4' cord
- Overload protection
- Safety covers
- Lighted switch

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
41378	078693413780	6-Outlet Corner Power Strip with 6' Cord	White	6	0	0	4	15A 120VAC 60Hz 1800W	6



### 6-Outlet Metal Power Strip with 5' Cord

- 2 Adapter outlets
- Overload protection
- 5' cord
- Safety covers
- Lighted switch

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
41386	078693413865	6-Outlet Metal Power Strip with 5' Cord	Dark Gray	6	0	0	5	15A 120VAC 60Hz 1800W	6



# Yard Master Outdoor Set - 5 Outlet with 25' 16/3 Outdoor Extension Cord

- 5-Outlet Power Adapter
- 16/3 SJTW 25 Foot Extension cord
- Addapter has impact resistant body, cord hook, overload protection, power on indicator
- Cord is weather resistant, with built-in cord strain relief, hi-visibility jacket
- Outdoor Rated Extension cord
- Value Pack

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41246	078693412462	Indoor/Outdoor Power Set	Black/ Green	6	0	0	25	0	15A 125VAC 60Hz 1875W	6



# **POWER STRIPS**





### 2-Outlet USB Strip with 3ft Cord

- 2 Grounded Outlets
- 2 USB-A ports
- 2.4 Amps
- 3 foot fabric cord
- 45 degree flat plug
- Wall mountable design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41283	078693412837	USB Power Strip	White	2	2 USB-A	2.4 A	3	0	15A 125VAC 60Hz 1875W	6





# 3-Outlet USB Strip with 1 USB-A and 1 USB-C 3' Cord

- 3 Grounded Outlets

- 1 USB-A at 3.1 Amps

- 1 USB-C fast charging port

- 3 foot extension cord

- 45 degree flat plug

- Wall Mountable design

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41284	078693412837	3 Outlet USB Strip	White	3	1 USB-A 1 USB-C	2.4 A	3	0	15A 125VAC 60Hz 1875W	6



### **6-OUTLET SURGE STRIP**

- Overload Protection
- LED indicator
- Safety covers

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41345	078693413452	6-Outlet 280J Surge Protector	White	6	0	0	1.5	280 Joules	15A 120VAC 60Hz 1800W	12
41346	078693413469	2 Pack 6-Outlet 280J Surge Protectors	White	4	0	0	2.5	280 Joules	15A 120VAC 60Hz 1800W	6
41492	078693414923	6-Outlet 510J Surge Protection	White	6	0	0	3	510 Joules	15A 120VAC 60Hz 1800W	6
41497	078693414978	6-Outlet 900J Surge Protector	White	6	0	0	3	900 Joules	15A 120VAC 60Hz 1800W	6
41446	078693414466	6-Outlet 680J Surge Protector	White	6	0	0	6	680 Joules	15A 120VAC 60Hz 1800W	6
41494	078693414947	6-Outlet 1440J Surge Protector	Black	6	0	0	4	1440 Joules	15A 120VAC 60Hz 1800W	6
41495	078693414954	6-Outlet 1780J USB Surge Protector	Black	6	2 USB-A	2.4 A	4	1780 Joules	15A 120VAC 60Hz 1800W	6



# 4-OUTLET DESKTOP SURGE STRIP WITH 4' CORD, 560 JOULES

- Desktop design
- 2.4 amps USB
- 4' cord
- Cord tucks into housin
- Lighted switch
- Overload protection
- Safety covers

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41379	078693413797	4-Outlet Desktop Corner USB Surge Protector	White	4	2 USB-A	2.4A	4	560 Joules	15A 120VAC 60Hz 1800W	6
41304	078693413049	4-Outlet 1180J USB Surge Protector	Black	4	2 USB-A	0	3	1180 Joules	15A 120VAC 60Hz 1800W	6
41515	078693414923	6-Outlet 1180J Surge Protector	Black	6	0	0	15	1180 Joules	15A 120VAC 60Hz 1800W	6



### 7-OUTLET SURGE STRIP

- Extra long 10' cord
- Right angle plug
- Overload protection
- LED indicators

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41626	078693416262	7-Outlet 1780J Surge Protector	Black	7	0	0	4	1780 Joules	15A 120VAC 60Hz 1800W	6
41496	078693414961	7-Outlet 1440J Surge Protector	Black	7	0	0	10	1440 Joules	15A 120VAC 60Hz 1800W	6
41627	078693416279	7-Outlet 2480J Surge Protector	Black	7	0	0	6	2480 Joules	15A 120VAC 60Hz 1800W	6



# 6-OUTLET METAL SURGE STRIP WITH 3' CORD, 900 JOULES

- Metal housing
- Overload protection
- Safety covers
- EMI/RFI noise filtration
- LED indicator
- Lighted switch

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41546	078693415463	6-Outlet Metal 900J Surge Protector	Dark Gray	6	0	0	3	900 Joules	15A 120VAC 60Hz 1800W	6



### 8-OUTLET SURGE STRIP

- Overload protection
- Right angle plug
- EMI/RFI noise filter
- LED indicators
- 3 adapter spaced outlets

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41618	078693416187	8-Outlet 3540J Surge Protector	Black	8	0	0	6	3560 Joules	15A 120VAC 60Hz 1800W	6
41629	078693416293	8-Outlet 3540J Surge Protector	Black	8	2 USB-A	2.4A	6	3540 Joules	15A 120VAC 60Hz 1800W	6



# 6-OUTLET SURGE STRIP WITH 3' CORD, 1780 JOULES

- 2.4 amps USB
- Overload protection
- Right angle plug
- LED indicators
- 2 USB Type-A ports

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41704	078693417047	6-Outlet 1780J Energy-Saving Surge Protector	White	6	0	0	3	1780 Joules	15A 125VAC 50/60Hz 1800W	6





# 6-OUTLET ENERGY SAVING SURGE STRIP WITH REMOTE, 5' CORD, 1080 JOULES

- Stops power loss
- EMI/RFI noise filter
- Remote control with 80' range
- Lighted switch

- Right angle plug
- Overload protection

Item Number	UPC	Item Description	Color	# of Outlets	USB Ports	Amps	Cord Length (in feet)	Joules of Surge Protection	Electrical Ratings	# items in Master Pack
41715	078693417153	6-Outlet 1080J Energy-Saving Surge Protector	White	6	0	0	5	1080 Joules	15A 120VAC 60Hz 1800W	6

# **HEAVY DUTY**



### 6-OUTLET STRIP WITH 8' CORD

- Overload protection
- High visibility cord
- Extra long 8' cord
- Lighted switch
- Mountable

Item Number	UPC	Item Description	Color	# of Outlets	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
4666	078693046667	6-Outlet Power Strip	Black	6	8	15A 125VAC 60Hz 1875W	12



### 9-OUTLET, 3' LONG POWER STRIP

- Metal/ABS housing
- Safety covers
- Overload protection
- Mountable
- Lighted switch

Item Number	UPC	Item Description	Color	# of Outlets	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
4609	078693046094	9-Outlet Power Strip	Black	9	3	15A 125VAC 60Hz 1875W	6



### 12-OUTLET, 6' LONG POWER STRIP

- Metal/ABS housing
- Safety covers
- Overload protection
- Mountable
- Lighted switch

Item Number	UPC	Item Description	Color	# of Outlets	Cord Length (in feet)	Electrical Ratings	# items in Master Pack
4612	078693046124	12-Outlet Power Strip	Black	12	6	15A 125VAC 60Hz 1875W	6



#