

Distributor List Price Sheet

**DF21****Flexible Conduit****Date: January 1, 2019**

Supersedes sheet DF20 - - Dated October 1, 2018

Prices shown are per 100 feet. Subject to change without notice.

**ARMORFLEX® TYPE RWA****REDUCED WALL ALUMINUM FLEXIBLE CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
5/16"	100	1000	6	0.510	<b>\$72.06</b>
3/8"	100	250 1000	7	0.610	<b>\$85.47</b>
1/2"	100	500 1000	9	0.920	<b>\$99.05</b>
3/4"	100	500 1000	13	1.105	<b>\$136.19</b>
1"	50	400	20	1.380	<b>\$256.63</b>
1 1/4"	50	250 400	24	1.630	<b>\$357.08</b>
1 1/2"	25	150 300	31	1.950	<b>\$511.38</b>
2"	25	100 150	40	2.454	<b>\$652.44</b>
2 1/2"	25	150	66	3.060	<b>\$839.31</b>
3"	25	100	77	3.560	<b>\$1,371.91</b>
3 1/2"	25	N/A	67	4.060	<b>\$1,583.52</b>
4"	25	N/A	76	4.560	<b>\$1,763.33</b>

**ALFLEX® TYPE SWA****STANDARD WALL DUAL LISTED UL/CSA ALUMINUM FLEXIBLE CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
1/2"	100	500 1000	15	0.920	<b>\$145.33</b>
3/4"	100	500 1000	20	1.105	<b>\$197.65</b>

**Southwire®**

Distributor List Price Sheet

**DF21****Flexible Conduit****GALFLEX® TYPE RWS****REDUCED WALL STEEL FLEXIBLE CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
5/16"	100	1000	13	0.510	<b>\$72.87</b>
3/8"	100 250	1000	19.2	0.610	<b>\$96.73</b>
1/2"	100	500 1000	27.2	0.920	<b>\$109.98</b>
3/4"	100	500 1000	34.6	1.105	<b>\$148.40</b>
1"	50	400	57	1.380	<b>\$270.30</b>
1 1/4"	50	250 400	65	1.630	<b>\$356.42</b>
1 1/2"	25	150 300	78	1.950	<b>\$569.74</b>
2"	25	100 150	133	2.454	<b>\$696.95</b>
2 1/2"	25	100 150	150	3.060	<b>\$847.99</b>
3"	25	100	190	3.560	<b>\$1,468.09</b>
3 1/2"	25	100	220	4.060	<b>\$1,649.60</b>
4"	25	100	270	4.560	<b>\$1,892.09</b>



**Flexible Conduit****DATA-FLEX®  
FLEXIBLE STEEL CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100 250	1000	14.4	0.585	<b>\$63.60</b>
1/2"	100	1000	22.1	0.875	<b>\$79.50</b>
3/4"	100	1000	28.1	1.075	<b>\$104.67</b>
1"	50	400	48.5	1.340	<b>\$221.28</b>
1 1/4"	50	250	55.1	1.590	<b>\$268.97</b>
1 1/2"	25	150	66	1.900	<b>\$523.37</b>
2"	25	100	93	2.400	<b>\$643.94</b>
2 1/2"	25	N/A	150	2.960	<b>\$780.42</b>
3"	25	N/A	190	3.460	<b>\$1,352.82</b>
3 1/2"	25	N/A	220	3.960	<b>\$1,534.33</b>
4"	25	N/A	270	4.460	<b>\$1,743.68</b>

**SLINKY-FLEX® TYPE SF  
EXTRA-FLEXIBLE CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
5/16"	100 250	N/A	13.6	0.472	<b>\$124.55</b>
3/8"	50 100 250	N/A	14.5	0.540	<b>\$139.13</b>
7/16"	100	N/A	16.2	0.610	<b>\$151.05</b>
1/2"	50 100 250	1000	19	0.665	<b>\$166.95</b>
9/16"	100	1000	23.8	0.728	<b>\$182.85</b>
3/4"	100	N/A	31.8	0.915	<b>\$200.08</b>



**Flexible Conduit****TITAN® TYPE UL****UL/CSA DUAL LISTED LIQUID-TIGHT FLEXIBLE METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	500 600	27	0.710	<b>\$166.19</b>
1/2"	100	500 1000	31.8	0.840	<b>\$222.92</b>
3/4"	100	500 1000	41.2	1.050	<b>\$303.38</b>
1"	100	400	77.6	1.315	<b>\$536.84</b>
1 1/4"	50	200 250	100.4	1.660	<b>\$709.63</b>
1 1/2"	50	150	97.9	1.900	<b>\$761.07</b>
2"	50	100	141.3	2.375	<b>\$991.90</b>
2 1/2"	25	100	182.5	2.875	<b>\$1,665.92</b>
3"	25	100	257	3.500	<b>\$2,000.95</b>
3 1/2"	25	100	294	4.000	<b>\$2,899.21</b>
4"	25	100	349.3	4.500	<b>\$3,161.70</b>

Standard Jacket Color: Gray  
 Also available in other colors: Subject to minimum runs..

**TITAN® Type CB****COMPUTER BLUE LIQUID-TIGHT FLEXIBLE METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	600	27	0.710	<b>\$176.75</b>
1/2"	100	500 1000	32.2	0.840	<b>\$237.43</b>
3/4"	100	500 1000	41.2	1.050	<b>\$323.16</b>
1"	100	400	77.6	1.315	<b>\$576.41</b>
1 1/4"	50	250	100.4	1.660	<b>\$749.21</b>
1 1/2"	50	150	97.9	1.900	<b>\$790.09</b>
2"	50	100	141.3	2.375	<b>\$1,034.11</b>
2 1/2"	25	100	182.5	2.875	<b>\$1,737.15</b>
3"	25	N/A	257	3.500	<b>\$2,076.14</b>
3 1/2"	25	N/A	294	4.000	<b>\$3,020.57</b>
4"	25	N/A	349.3	4.500	<b>\$3,279.09</b>

Standard Jacket Color: Blue



**Flexible Conduit****TITAN® TYPE HC****HOT/COLD LIQUIDTIGHT FLEXIBLE METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	600	27	0.710	<b>\$214.28</b>
1/2"	100	1000	31	0.840	<b>\$290.83</b>
3/4"	100	1000	40	1.050	<b>\$397.96</b>
1"	100	400	76	1.315	<b>\$668.39</b>
1 1/4"	50	250	102	1.660	<b>\$877.56</b>
1 1/2"	50	150	103	1.900	<b>\$1,086.76</b>
2"	50	100	145	2.375	<b>\$1,214.30</b>
2 1/2"	25	N/A	197	2.875	<b>\$2,346.96</b>
3"	25	N/A	265	3.500	<b>\$2,882.69</b>
3 1/2"	25	N/A	300	4.000	<b>\$4,336.79</b>
4"	25	N/A	333	4.500	<b>\$4,591.89</b>

Standard Jacket Color: Gray

**TITAN® TYPE EF****EXTRA-FLEXIBLE LIQUID-TIGHT METALLIC CONDUIT - STEEL CORE**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	500 600	23.1	0.710	<b>\$122.66</b>
1/2"	100	500 1000	22.5	0.840	<b>\$141.13</b>
3/4"	100	500 1000	29.5	1.050	<b>\$182.03</b>
1"	100	400	54	1.315	<b>\$267.76</b>
1 1/4"	50	250	69.5	1.660	<b>\$346.90</b>
1 1/2"	50	150	90.5	1.900	<b>\$655.56</b>
2"	50	100	130.9	2.375	<b>\$757.11</b>
2 1/2"	25	150	167.2	2.875	<b>\$1,412.67</b>
3"	25	100	211.5	3.500	<b>\$1,734.52</b>
3 1/2"	25	100	267.6	4.000	<b>\$2,644.64</b>
4"	25	100	300.2	4.500	<b>\$2,805.56</b>

Standard Jacket Color: Gray  
Also available in other colors: Subject to minimum runs..



**Flexible Conduit****ULTRATITE® TYPE NM**  
**LIQUID-TIGHT NON-METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	600	10.5	0.710	<b>\$81.22</b>
1/2"	100	1000	12.9	0.840	<b>\$87.49</b>
3/4"	100	1000	18.8	1.050	<b>\$122.05</b>
1"	100	400	25.9	1.315	<b>\$194.71</b>
1 1/4"	50	250	30.9	1.660	<b>\$288.17</b>
1 1/2"	50	150	44.6	1.900	<b>\$359.08</b>
2"	50	100	62	2.375	<b>\$494.46</b>

Available also in Black

**ULTRATITE® TYPE NMOR****OIL RESISTANT LIQUID-TIGHT FLEXIBLE NON-METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	600	10.8	0.710	<b>\$84.51</b>
1/2"	100	1000	12.7	0.840	<b>\$91.20</b>
3/4"	100	1000	18.1	1.050	<b>\$124.56</b>
1"	100	400	26.2	1.315	<b>\$204.62</b>
1 1/4"	50	250	32.7	1.660	<b>\$284.70</b>
1 1/2"	50	150	45.2	1.900	<b>\$371.45</b>
2"	50	100	63.1	2.375	<b>\$529.37</b>

**ULTRATITE® TYPE NMHC****HOT/COLD LIQUID-TIGHT FLEXIBLE NON-METALLIC CONDUIT**

TRADE SIZE	Feet Per Coil	Feet Per Reel	Weight (lbs) Per 100 ft.	Overall Diameter (inches)	Price Per 100 ft.
3/8"	100	600	10.5	0.710	<b>\$253.56</b>
1/2"	100	1000	12.9	0.840	<b>\$273.58</b>
3/4"	100	1000	18.8	1.050	<b>\$373.66</b>
1"	100	400	25.9	1.315	<b>\$613.87</b>
1 1/4"	50	250	30.9	1.660	<b>\$854.08</b>
1 1/2"	50	150	44.6	1.900	<b>\$1,114.32</b>
2"	50	100	62	2.375	<b>\$1,588.07</b>



---

**Flexible Conduit**

---

**PAYMENT TERMS**

Terms are 2% 10<sup>th</sup> prox. month, net end of prox. month. Cut off dates have been moved from the 25th to the 30th. Any invoices with dates for days 1 - 30 of a month are due with discount by the 10th of the month following the invoice month, and are due net by the last day of the month following the invoice month. (Example: Invoice date of 03/30, due with discount on 04/10, and due net by 04/30) Any invoices dated the 31st of a month are due with discount by the 10th of the second month following the invoice month, and are due net by the last day of the second month following the invoice month. (Example: Invoice date of 03/31, due with discount on 05/10, and due net by 05/31.)

**ORDER ACCEPTANCE**

Orders are binding only after acceptance by the General Office in Carrollton and all transactions are subject to Southwire's General Terms and Conditions. Orders will be invoiced on date of shipment.

**MINIMUM ORDER**

The minimum order amount is \$500 and can be any combination of products.

**DELIVERY TERMS**

Orders of 500 pounds or more net weight will be f.o.b. destination with freight prepaid and allowed, within the continental United States only. Orders f.o.b. ports of Alaska or Hawaii are subject to an additional shipping cost. Rates for "Prepay and Charge" orders are based on the (1994) Yellow YFSY 500M tariff with a 30% discount, with an absolute minimum charge of \$72.00. For Prepaid Freight information for combinations of products, please see the "Electrical Division Freight Policy" on the southwire.com home page, or the "Document Summary" from the internet price sheet page, or you may contact your sales representative.

**RETURN GOODS REQUEST**

Southwire Flexible Conduit products are carefully manufactured and tested. Should our products prove defective, or appear to be so, please discontinue use immediately and notify us so an inspection can be made. We cannot be responsible for any damages or claims beyond the selling price of our products.

**FOR ADDITIONAL INFORMATION**

For General Terms and Conditions of Sale see Catalog Section 63. For additional information on these or any other Southwire products, contact your Southwire representative, Southwire Company Distributor Sales in Carrollton, Georgia, or [www.southwire.com](http://www.southwire.com).



Carrollton, Georgia 30119-0001, USA  
Phone: (770) 832-4257