




Southwire®



FIRE ALARM CABLE IS NOW COMPLETELY SPOOL-PROOF

INCREASE SAFETY AND PRODUCTIVITY

- SIMpull® NoLube® wire jacket
- Durable package fully encases & helps protect wire
- Built-in handle
- Payoff directly from package. Reduce setup.
- No more broken spools
- Designed to help reduce potential lifting/handling/pulling injuries
- Innovative design reduces pulling effort, no over-spin
- Designed to help increase productivity



FPLP			
PART #	CONSTRUCTION	LENGTH	JACKET COLOR
G40005-1G	18/2 Sol BC NS FPLP	1,000	Red
G50032-1G	16/2 Sol BC NS FPLP	#2 -1500	Red
G60004-1G	14/2 Sol BC NS FPLP	#2 -1500	Red
G40006-1G	18/2 Sol BC OAS FPLP	#2 -1500	Red
G50013-1G	16/2 Sol BC OAS FPLP	#2 -1500	Red
G60025-1G	14/2 Sol BC OAS FPLP	#2 -1500	Red

FPLR			
PART #	CONSTRUCTION	LENGTH	JACKET COLOR
F40021-1G	18/2 Sol BC NS FPLR	1,000	Red
F50004-1G	16/2 Sol BC NS FPLR	#2 -1500	Red
F60001-1G	14/2 Sol BC NS FPLR	#2 -1500	Red
F40015-1G	18/2 Sol BC OAS FPLR	#2 -1500	Red
F50010-1G	16/2 Sol BC OAS FPLR	#2 -1500	Red
F60030-1G	14/2 Sol BC OAS FPLR	#2 -1500	Red

Contact your Southwire Representative for additional options, including additional jacket colors.



Southwire®



YOU CAN NOW ROLL OUT FIRE ALARM CABLE IN A BARREL

TAPPAN™ FIRE ALARM CABLE IN A SIMpull BARREL™ CABLE DRUM

- Minimal pulling tension required
- SIMpull® NoLube® wire jacket eliminates any need to lube, resulting in more efficient pulls
- No over-spin, reducing labor
- Durable package encases wire for protection
- Payoff directly from package. Reduce setup.
- No broken spools
- Less scrap



The 42" barrel is featured with SIMpull BARREL™ Hand Truck, Model #SBT01

FPLP				
PART #	CONSTRUCTION	LENGTH	DRUM HEIGHT	WEIGHT IN LBS
G40006-1N	18/2 Sol BC OAS FPLP Red	2,500	22"	57
G50032-1N	16/2 Sol BC NS FPLP Red	2,500	22"	74
G60004-1N	14/2 Sol BC NS FPLP Red	2,500	22"	102
Separator				
G40006-1ZN	18/2 Sol BC OAS FPLP Red	10,000	30"	190
G50032-1ZN	16/2 Sol BC NS FPLP Red	10,000	30"	240
G60004-1ZN	14/2 Sol BC NS FPLP Red	10,000	42"	360

FPLP				
PART #	CONSTRUCTION	LENGTH	DRUM HEIGHT	WEIGHT IN LBS
F60001-1N	14/2 Sol BC NS FPLR Red	2,500	22"	97
Separator				
F40021-1ZN	18/2 Sol BC NS FPLR Redd	10,000	22"	151
F40015-1ZN	18/2 Sol BC OAS FPLR Red	10,000	30"	180
F50004-1ZN	16/2 Sol BC NS FPLR Red	10,000	30"	210
F60001-1ZN	14/2 Sol BC NS FPLR Red	10,000	42"	350

Contact your Southwire Representative for additional options, including additional jacket colors.