

Steel Reel Policy

Steel Reel Policy

Steel reels are often required for transportation and storage of product. Each reel has an associated charge.

1. Reels are to be returned based on terms on invoice. Upon reel return within stated terms, a credit will be issued for the amount of the original reel invoice – including sales tax, if applicable. If the reel is not returned within terms stated on invoice of the original shipment, the customer will forfeit any future credit for the reel. If the reel invoice is not paid, the invoice will become delinquent on the customer's account.
2. Reels should be returned in good condition. Normal wear is expected; charges are made only for "exceptional damage" (that which makes the reel unusable through abuse or unauthorized modifications) as determined by Southwire.
3. Prompt notification of reels available for return should be given to Southwire's Steel Reel Manager at swreels@southwire.com or www.southwire.com/reel-data. Phone calls do not provide adequate means for verification of return requests, and therefore are not a permissible method for making such requests. The given methods provide a verification email that should be retained by the customer should the need arise to confirm the date of initial return requests.

Notifications should specify:

- a. Original consignee
 - b. Date shipped
 - c. Reel invoice number
 - d. Serial numbers of reels to be returned
4. No reels should be returned without prior consent from Southwire. Upon consenting to the return, Southwire will provide customer with complete shipping instructions. Charges incurred over and above the least-cost method of return (as determined by Southwire) by unauthorized return shipments may be charged to the customer.
 5. To accommodate larger projects or conductor shipments in advance of project start, a reel charge deferral period may be negotiated at time of quotation. The above-described 90- day term would start at the end of the agreed upon deferral period rather than the initial ship date. Requests for a deferral or an extension to an existing deferral after the order has been processed must be made in writing and will be reviewed by Southwire in consideration of granting the request.
 6. Processing reel return requests and accepting the reel return does not constitute, and should not be viewed by the customer, as a guarantee that the reel will be credited if the 90-day period has lapsed.

Steel Reel Policy

Reel Designation		Dimensions (inches)					Approx. Weight (lbs)	Charges
Alum, Assoc.+	SW Class	Flange	Traverse	Drum	Max. Overall Width	Arbor Hole		
	S-1013	158	86	90	95.5	7.625	4598	\$16,710.00
	S-1100	158	83	80	94.5	7.625	3941	\$21,060.00
RMT 84.36	S-120	84	36	42	43	5.25	895	\$2,340.00
RMT 84.45	S-153	84	45	42	52.5	5.25	930	\$2,400.00
RMT 90.45	S-187	90	45	42	52.5	5.25	1030	\$2,600.00
	S-224	90	45	42	52.5	5.25	984	\$2,470.00
	S-235	90	44	38	52	5.25	990	\$2,930.00
	S-249	90	60	42	68	5.25	1176	\$2,690.00
	S-282	90	60	46	68	5.25	1268	\$2,470.00
	S-299	90	60	42	68	5.25	1016	\$2,800.00
RMT 96.60	S-300	96	60	42	68	5.25	1082	\$2,800.00
	S-300A	96	60	42	68	5.313	1573	\$4,290.00
	S-400	110	70	60	78	5.25	1770	\$4,160.00
	S-422	108	74	56	82	5.25	1762	\$4,160.00
	S-431	118	85	78	94.5	7.625	3677	\$10,080.00
	S-435	102	68	47	77.37	5.25	1278	\$3,640.00
	S-600	118	85	60	94.5	7.625	2825	\$8,650.00
	S-62	60	28	28	34.5	3	340	\$1,240.00
	S-622	126	86	72	95	7.625	3494	\$9,620.00
	S-650	138	85	88	94.5	7.625	4075	\$11,250.00
	S-740	138	85	80	94.5	7.625	3654	\$10,990.00
RM 66.32	S-77	66	32	36	38	3	400	\$1,370.00
	S-869	158	86	110	95.5	7.625	3504	\$10,080.00
	S-906	158	88	100	94.6	5.25	6945	\$14,170.00
RM 68.38	S-99	68	38	36	44.75	3.125	444	\$1,500.00

+ "RM" is the Aluminum Association code designation for returnable metal reels, and "RMT" is for returnable metal reels with I-beam tires.