



Southwire™

SERVICE ENTRANCE CATALOG



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

SOUTHWIRE.COM

SERVICE ENTRANCE FITTINGS

Southwire Service Entrance products provide easy access for installation of Electrical service or maintenance. Service entrance caps are available in threaded, PVC, clamp on with split insulator and set screw type to protect service entrance cables. Meter hubs, Duct Seal and flashings are also available to secure and protect conduit and ventilation pipes.

Aluminum Service Entrance Caps – Clamp on
Aluminum Service Entrance Caps – Threaded

PVC Service Entrance Caps

Roof Flashings

Meter Hubs

Sill Plates

Duct Seal

Porcelain Wire holders

Utility Pole Brackets

Watertight Compression Connectors



SE/SEU STRAPS

ONE HOLE - ALUMINUM



232A

| PART # | WIRE SIZES | INNER QTY. | MASTER QTY. |
|--------|----------------|------------|-------------|
| 232A | 3 #3 OR #2 | 100 | 1000 |
| 282A | 3 #1/0 OR #2/0 | 25 | 250 |
| 284A | 3 #3/0 OR #4/0 | 20 | 100 |

FEATURES

- One hole
- Wide wire range
- Stamped aluminum

APPLICATIONS

- Use to secure SE & SEU service entrance cable in surface mount applications

STANDARD MATERIAL

- Aluminum

TWO HOLE - GALVANIZED STEEL



506

| PART # | WIRE SIZES | INNER QTY. | MASTER QTY. |
|--------|------------|------------|-------------|
| 506 | 3#8, 6, 4 | 100 | 1000 |
| 507 | 3#3, 2 | 100 | 1000 |
| 508 | 3#1/0, 2/0 | 25 | 250 |
| 509 | 3#3/0, 4/0 | 25 | 250 |

FEATURES

- Inverted rib provides strength to keep cable secure
- Snap-on Rigid strap with two holes

APPLICATIONS

- Use to secure SE & SEU service entrance cable in surface mount applications

STANDARD MATERIAL

- Galvanized steel

ONE HOLE NM STRAP



510RX

| PART # | WIRE SIZES | INNER QTY. | MASTER QTY. |
|--------|---|------------|-------------|
| 510RX | 14, 12, 10 IN 2 OR 3 CONDUCTOR, WITH OR WITHOUT GROUND. ALSO 14 IN UF | 100 | 1000 |

FEATURES

- One hole
- Inverted rib provides strength to keep cable secure

APPLICATIONS

- Use to secure Romex® Brand nonmetallic sheathed cable in surface mount applications

STANDARD MATERIAL

- Steel


STANDARD FINISH

- Zinc plated

SE LOCK OVER CLIPS



135



FEATURES

- Securely attaches cable to fascia board

APPLICATIONS

- Fast and easy installation for service entrance cables

STANDARD MATERIAL


- Aluminum

| PART # | SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|------|------------|-------------|---------------------|-------|------|
| 136 | 4/3 | 100 | 1000 | 10 | 1.52" | .75" |
| 137 | 2/3 | 100 | 1000 | 15 | 1.62" | .75" |
| 138 | 2/0 | 50 | 500 | 20 | 1.82" | .89" |
| 139 | 4/0 | 50 | 500 | 25 | 2.20" | 1" |

SERVICE ENTRANCE HOODS



709



FEATURES

- Constructed of crush proof PVC
- Eliminates sharp edges to avoid abrasion

APPLICATIONS

- Required in overhead applications

STANDARD MATERIAL

- PVC

CERTIFICATIONS

- UL

| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|-----------|-------------|---------------------|-------|-------|-------|
| 709 | 3#3-1 | 10 | 5 | .425" | 5" | 2" |
| 710 | 3#2/0-4/0 | 10 | 6 | 6" | 5.19" | 2.50" |

RIGID OFFSET REDUCERS



1203

FEATURES

- Reduces conduit size to accommodate an existing knockout
- To offset the raceway

APPLICATIONS

- Add space to move conduit further away from wall

STANDARD MATERIAL

- Aluminum


| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) |
|--------|-------------|-------------|---------------------|
| 1203 | 2" x 1-1/4" | 50 | 22 |
| 1204 | 2-1/2" x 2" | 25 | 21 |

SERVICE ENTRANCE CAPS

CLAMP ON TYPE



731



FEATURES

- Provides water resistant cap to protect service entrance cables
- Clamp on style for unthreaded conduit

APPLICATIONS

- Use in an overhead service entrance
- Mounts on top of EMT, Rigid, or IMC conduit
- Serves as a connecting point for the service entrance wires

STANDARD MATERIAL

- Aluminum
- Steel strap

CERTIFICATIONS

- cULus


| PART # | SIZE | INSIDE HOLE SIZE | # HOLES | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|--------|-------------------------|-------------|------------|-------------|---------------------|--------|-------|-------|
| 731 | 1/2" | 19/64" | 4 | 10 | 50 | 9 | 2.93" | 2.62" | 2" |
| 732TZ | 3/4" | 3/8" 13/32" | 2 3 | 10 | 50 | 13 | 3.25" | 2.75" | 2.37" |
| 733 | 1" | 7/16" 1/2" | 2 3 | 5 | 25 | 8 | 3.50" | 3.25" | 2.62" |
| 734 | 1-1/4" | 27/64" 5/8" | 2 3 | 5 | 25 | 12 | 4.50" | 3.25" | 3" |
| 735 | 1-1/2" | 19/32" 7/16" 3/4" | 2 1 3 | 3 | 15 | 10 | 5" | 4.75" | 3.31" |
| 736 | 2" | 17/32" 3/4" 1" | 1 2 3 | --- | 5 | 5 | 6.75" | 6" | 4.62" |
| 737 | 2-1/2" | 7/8" 1" 1-5/16" | 3 1 3 | --- | 1 | 3 | 10.50" | 7.50" | 6" |
| 738 | 3" | 7/8" 1" 1-5/16" | 3 1 3 | --- | 1 | 3 | 11.50" | 9" | 8" |
| 739 | 3-1/2" | 1-1/8" 1-3/4" | 4 3 | --- | 1 | 5 | 12" | 9" | 8" |
| 740 | 4" | 1-1/8" 1-3/4" | 4 3 | --- | 1 | 4 | 12" | 9" | 8" |

SERVICE ENTRANCE CAPS

THREADED TYPE



741



FEATURES

- Provides water resistant cap to protect service entrance cables
- Threaded style enables easy installation

APPLICATIONS

- Use in an overhead service entrance
- Mounts on top of Rigid, or IMC conduit
- Serves as a connecting point for the service entrance wires

STANDARD MATERIAL

- Aluminum

CERTIFICATIONS

- cULus


| PART # | SIZE | INSIDE HOLE SIZE | # HOLES | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|--------|-------------------------|-------------|------------|-------------|---------------------|--------|-------|-------|
| 741 | 1/2" | 19/64" | 4 | 5 | 50 | 12 | 2.68" | 2.60" | 2" |
| 742 | 3/4" | 3/8" 13/32" | 2 3 | 5 | 50 | 15 | 3.80" | 2.72" | 2.37" |
| 743 | 1" | 7/16" 1/2" | 2 3 | --- | 50 | 15 | 3.32" | 3.11" | 2.62" |
| 744 | 1-1/4" | 27/64" 5/8" | 2 3 | --- | 20 | 10 | 4.46" | 3.20" | 3" |
| 745 | 1-1/2" | 19/32" 7/16" 3/4" | 2 1 3 | --- | 10 | 7 | 4.85" | 4.34" | 3.31" |
| 746 | 2" | 17/32" 3/4" 1" | 1 2 3 | --- | 5 | 4 | 6.62" | 5.44" | 4.62" |
| 747 | 2-1/2" | 7/8" 1" 1-5/16" | 3 1 3 | --- | 2 | 8 | 9.74" | 7.80" | 6" |
| 748 | 3" | 7/8" 1" 1-5/16" | 3 1 3 | --- | 1 | 6 | 10.50" | 8" | 8" |
| 749TZ | 3-1/2" | 1-1/8" 1-3/4" | 4 3 | --- | 1 | 6 | 13.02" | 9.39" | 8" |
| 750 | 4" | 1-1/8" 1-3/4" | 2 4 | --- | 1 | 7 | 13.14" | 8.54" | 8" |
| 750A | 5" | 1-1/8" 1-3/4" | 2 4 | --- | 1 | 12 | 11.28" | 8.77" | 8.25" |
| 750B | 6" | 1-1/8" 1-3/4" | 2 4 | --- | 1 | 14 | 12.25" | 9.76" | 8.25" |

SERVICE ENTRANCE CAPS

PVC



727



FEATURES

- Heavy duty construction
- Snap on cover

APPLICATIONS

- Use as a connecting point in an overhead service entrance for SEU cable
- Fits 2/3, 3#2/0 and #4/0 cables

STANDARD MATERIAL


- PVC

| PART # | FITS CABLE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|-------------|-------------|---------------------|------|------|------|
| 727 | 2/3 | 30 | 8 | 2.75 | 2.75 | 1.87 |
| 729 | 3#2/0, #4/0 | 10 | 11 | 4.25 | 4.25 | 3 |

CLAMP ON WITH SPLIT INSULATOR



707



FEATURES

- Provides water resistant cap when mounted on conduit
- Eliminates sharp edges to protect wire

APPLICATIONS

- Required in overhead applications
- Fits 3#8 to 3#1 and #1/0 to 4/0 cables

STANDARD MATERIAL


- Zinc die cast
- Steel strap

| PART # | FITS CABLE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|------------|-------------|---------------------|-------|-------|-------|
| 707 | 3#8 TO 3#1 | 20 | 8 | 2.37" | 2.25" | 2.25" |
| 708 | 1/0 TO 4/0 | 10 | 11 | 4.93" | 3.12" | 3.75" |

SET SCREW TYPE



704TZ



FEATURES

- Eliminates sharp edges to protect wire
- Extended hood

APPLICATIONS

- Required in overhead applications
- For 2" to 2-1/2" pipe sizes

STANDARD MATERIAL

- Aluminum

CERTIFICATIONS

- UL

| PART # | PIPE SIZE | HEAD SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|-----------|-----------|-------------|---------------------|-------|-------|-------|
| 704TZ | 2" | 1-1/4" | 10 | 10 | 4.75" | 4" | 3.12" |
| 705TZ | 2-1/2" | 1-1/4" | 10 | 20 | 5.25" | 4" | 3" |
| 706TZ | 2-1/2" | 2" | 10 | 20 | 7" | 5.50" | 4.50" |

ROOF FLASHINGS

GALVANIZED WITH NEOPRENE SEAL



| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|--------|-------------|---------------------|--------|--------|
| 984TZ | 1-1/4" | 25 | 18 | 12.50" | 8.75" |
| 985TZ | 1-1/2" | 25 | 24 | 12.50" | 8.375" |
| 986TZ | 2" | 25 | 24 | 14.50" | 10.75" |
| 987 | 2-1/2" | 25 | 25 | 14.50" | 10.75" |

FEATURES

- Strong galvanized steel with neoprene seal
- Flexible collar

APPLICATIONS

- Watertight protection for service entrance conduit or ventilation pipes
- Directs water flow away from riser pipe entry point


STANDARD MATERIAL

- Galvanized steel
- Neoprene seal

CERTIFICATIONS

- UL

NEOPRENE



| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|-----------------|-------------|---------------------|--------|--------|
| 994TZ | 1-1/4" - 1-1/2" | 12 | 5 | 12.50" | 8.75" |
| 995TZ | 2" | 12 | 5 | 12.50" | 8.375" |
| 996 | 2-1/2" | 12 | 5 | 14.50" | 10.75" |
| 997 | 3" | 12 | 6 | 14.50" | 10.75" |

FEATURES

- Repels weather related damage from snow, ice and rain
- No caulking required
- Durable neoprene construction

APPLICATIONS

- Watertight protection for service entrance conduit or ventilation pipes
- Directs water flow away from riser pipe entry point

STANDARD MATERIAL

- Neoprene

CERTIFICATIONS

- UL

NO-CAULK



P-339

FEATURES

- Flashing base and collar are separate
- Fits flat surface up to 45 deg pitch
- For plastic, cast iron, or galvanized pipe

APPLICATIONS

- Prevents water leaks where conduit enters roof surface

STANDARD MATERIAL

- 24 gauge galvanized steel base, elastomeric compound collar

UNIVERSAL



P-400

FEATURES

- Conforms to uneven surfaces for a tight seal
- Conforms to uneven surfaces for a tight, dry seal pipe

APPLICATIONS

- Prevents water leaks where conduit enters roof surface

STANDARD MATERIAL

- Heavy-duty aluminum alloy base, elastomeric compound collar


| PART # | SIZE | MASTER QTY. |
|--------|------------------|-------------|
| P-339 | 1-1/4" TO 1-1/2" | 12 |
| P-340 | 2" | 12 |
| P-342 | 3" | 12 |
| P-344 | 4" | 12 |

| PART # | SIZE | MASTER QTY. |
|--------|--------------|-------------|
| P-400 | 1-1/4" TO 4" | 6 |

METER HUBS



9663



FEATURES

- Includes hardware
- Corrosion resistant construction withstands inclement weather
- Mounting hole space is 2.5" on center

APPLICATIONS

- Attach to meter boxes or enclosures to provide threaded opening for conductors

STANDARD MATERIAL

- Zinc die cast


| PART # | SIZE | MASTER QTY. | WEIGHT/CASE (LBS.) | A | B |
|--------|--------|-------------|--------------------|-------|-------|
| 9663 | 1" | 10 | 3 | 3.25" | 3.25" |
| 9674 | 1-1/4" | 10 | 2 | 3.25" | 3.25" |
| 9685 | 1-1/2" | 10 | 2 | 3.25" | 3.25" |
| 9696 | 2" | 10 | 2 | 3.25" | 3.25" |
| 9707 | 2-1/2" | 10 | 2 | 3.25" | 3.25" |

SILL PLATES

ZINC DIE CAST



591TZ



FEATURES

- Accompanying sealing compound and screws ensures watertight seal
- Domed top offers maximum protection

APPLICATIONS

- Protects wires and aluminum entry holes
- Sizes for EMT and SEU

STANDARD MATERIAL

- Zinc die cast

| PART # | SIZE | INNER QTY. | MASTER QTY. | WEIGHT/CASE (LBS.) | A | B | C |
|--------|----------------------|------------|-------------|--------------------|--------|--------|--------|
| 591TZ | 1/2" EMT & 3/4" EMT | 10 | 100 | 10 | 2.37" | 1" | 2.61" |
| 593 | 1" EMT & 3/3 SEU | 10 | 100 | 40 | 2.50" | 1.25" | 3" |
| 594 | 1-1/4" EMT & 2/3 SEU | --- | 25 | 15 | 2.61" | 1.56" | 3.76" |
| 595 | 1-1/2" EMT | --- | 25 | 11 | 3.580" | 1.738" | 3.568" |
| 596 | 4/0 SEU | --- | 20 | 17 | 5.81" | 1.88" | 3.48" |
| 596A | 2" EMT | --- | 25 | 16 | 4.20" | 2.29" | 4.76" |

PVC (1900) AND ALUMINUM (ME14)



1900

FEATURES

- Corrosion resistant

APPLICATIONS

- Prevents water from entering structure when used with sealing compound (Southwire parts 1901 or 1905)

STANDARD MATERIAL

- PVC (1900) and Aluminum (ME14)

| PART # | CABLE RANGE | INNER QTY. | MASTER QTY. |
|--------|-------------|------------|-------------|
| 1900 | #4 - 0 | 10 | 100 |
| ME14 | #3/0 - 4/0 | --- | 5 |

DUCT-SEAL WEATHERPROOF COMPOUND

GRAY, ASBESTOS FREE



961



FEATURES

- Permanently soft
- Non-corrosive to metals or plastics; will not harm skin
- Adheres to clean surfaces

APPLICATIONS

- Forms water and air tight seals around junction boxes
- Deadens switch gear panel noise

STANDARD MATERIAL

- Non toxic compound; asbestos free

CERTIFICATIONS


- UL

| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) |
|--------|-------|-------------|---------------------|
| 961 | 1 LB. | 50 | 50 |
| 965TZ | 5 LB. | 10 | 50 |

SERVICE ENTRANCE ELLS-SLB



211TZ



FEATURES

- Provides easy access for service
- Includes cover and gasket

APPLICATIONS

- Enables effortless wire pulling when raceway alters direction

STANDARD MATERIAL

- Die cast copper free aluminum

CERTIFICATIONS

- UL


| PART # | SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|-------------|------------|-------------|---------------------|--------|--------|---------|
| 211TZ | 1/2" | 10 | 50 | 13 | 3.155" | 1.187" | 1.375" |
| 212 | 3/4" | 10 | 50 | 16 | 3.47" | 1.36" | 1.625" |
| 213TZ | 1" | 5 | 25 | 12 | 4.18" | 1.72" | 1.9375" |
| 214 | 1-1/4" | 2 | 10 | 8 | 5.515" | 2.178" | 2.4375" |
| 214XL | 1-1/4" LONG | --- | 2 | 3 | 6.095" | 2.41" | 2.6875" |
| 215 | 1-1/2" | 1 | 5 | 6 | 6.595" | 2.846" | 3.0625" |
| 216 | 2" | 1 | 5 | 10 | 7.91" | 2.75" | 2.75" |
| 216XL | 2" LONG | --- | 1 | 3 | 7.74" | 3.88" | 3.375" |

SERVICE ENTRANCE CABLE FITTINGS

KENNY CLAMPS



1750



FEATURES

- Use as a grounding and bonding connector
- 1/2" knockout

APPLICATIONS

- Bonds a grounding electrode conductor to metallic conduit panel boards or transformer enclosures

STANDARD MATERIAL

- Brass

CERTIFICATIONS

- UL


| PART # | SIZE | KO SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|--------------|---------|------------|-------------|---------------------|-------|---------|
| 1750 | 3/0 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1751 | 2/0 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1752 | 1/0 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1753 | 2 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1754 | 4 SOLID | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1755 | 4 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1756 | 6 SOLID | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1757 | 6 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1758 | 8 SOLID | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |
| 1759 | 8 STRANDED | 1/2" | 10 | 100 | 35 | 1.75" | 1.0625" |

WIRESHOLDERS

ADJUSTABLE



999



FEATURES

- Corrosion resistant and electro-galvanized finish ensure a long product life in all climates
- The unique design allows for safe and secure installation of power drop cables on the outside of buildings

APPLICATIONS

- Protects sheathing and ensures performance

STANDARD MATERIAL

- Porcelain/steel

STANDARD FINISH


- Steel parts are electro-galvanized

| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C |
|--------|-------------|-------------|---------------------|-------|-------|------------|
| 999 | 1-1/4" - 3" | 20 | 34 | 7.62" | 5.60" | 1" X .875" |

LIGHT DUTY WITH LAG SCREW



1001TZ



FEATURES

- Light duty
- Includes lag screw
- Single-point wireholders are strong and compact
- Heavy cup-base and strap is a single steel stamping, to which the screw is rigidly assembled

APPLICATIONS

- Secure wires before entry into a mast or SE cap

STANDARD MATERIAL

- Porcelain/steel


| PART # | LAG | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C | D |
|--------|----------|-------------|---------------------|---------|--------|-------------|--------|
| 1001TZ | 1-11/16" | 100 | 25 | 3.0625" | 1.375" | .5" X .375" | 1.687" |

WIREHOLDERS

MEDIUM DUTY WITH LAG SCREW



1002



FEATURES

- Medium duty
- Includes lag screw
- Single-point wireholders are strong and compact
- Heavy cup-base and strap is a single steel stamping, to which the screw is rigidly assembled

APPLICATIONS

- Secure wires before entry into a mast or SE cap

STANDARD MATERIAL


- Porcelain/steel

| PART # | LAG | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C | D |
|--------|--------|-------------|---------------------|-------|--------|-------------|-------|
| 1002 | 2-1/4" | 50 | 32 | 5.25" | 1.968" | .5" X .375" | 2.25" |

SERVICE INSULATOR WIRE HOLDERS



P-19



FEATURES

- Secures incoming wires for overhead service entrance cable

STANDARD MATERIAL


- Porcelain

| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C | D |
|--------|---------------|-------------|---------------------|-------|--------|-----------|-------|
| P-16 | 3/8" x 2-1/4" | 50 | .626 | 5.41" | 1.875" | 3/8" | 2.25" |
| P-19 | 3/8" x 3" | 50 | .76 | 6.15" | | | 3" |
| P-20 | 3/8" x 4" | 25 | .626 | 7.15" | | | 4" |

HEAVY DUTY WITH LAG SCREW



1003



FEATURES

- Heavy duty
- Includes lag screw
- Single-point wireholders are strong and compact
- Heavy cup-base and strap is a single steel stamping, to which the screw is rigidly assembled

APPLICATIONS

- Secure wires before entry into a mast or SE cap

STANDARD MATERIAL


- Porcelain/steel reinforced

| PART # | LAG | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C | D |
|--------|--------|-------------|---------------------|---------|--------|------------|-------|
| 1003 | 2-1/4" | 50 | 34 | 6.1563" | 1.875" | 1" x .875" | 2.25" |

SERVICE ENTRANCE CABLE FITTINGS

WIRESHOLDERS

HEAVY DUTY



FEATURES

- Heavy duty for optimal performance
- Protects sheathing
- Bolt or hanger assembly

APPLICATIONS



- Secure wires before their entry into a mast or SE cap

STANDARD MATERIAL

- Porcelain/steel

| PART # | BOLT SIZE | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C | D |
|--------|-----------|------|-------------|---------------------|--------|--------|------------|--------|
| 1004 | 3/8" x 5" | --- | 25 | 22 | 8.156" | 1.875" | 1" x .875" | 5" |
| 1008 | HANGER | 2" | 25 | 31 | 6.416" | 1.875" | 1" x .875" | 3.375" |

WEDGE GRIP CLAMPS



FEATURES

- Solid 6-1/2" stainless steel bail
- High quality aluminum for durability

APPLICATIONS



- Supports power cables and other conductors when attached to buildings or utility poles

STANDARD MATERIAL

- Steel reinforced aluminum conductor

| PART # | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | OPENING C |
|--------|---------------------|-------------|---------------------|-------|-------|-----------|
| 1005TZ | 6 ACSR – 2 ACSR | 50 | 8 | 3" | 6.07" | 5.45" |
| 1006 | 4 ACSR – 1/0 ACSR | 25 | 7 | 3.75" | 7.26" | 5.45" |
| 1007 | 2/0 ACSR – 4/0 ACSR | 25 | 8 | 3.75" | 7.28" | 5.45" |

UNIVERSAL PIPE SUPPORT



FEATURES

- 10" bolt
- High strength construction

APPLICATIONS

- Secure pipe sizes 1-1/4" to 3"

STANDARD MATERIAL

- Steel

| PART # | BOLT SIZE | SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B | C |
|--------|-------------|------|-------------|---------------------|--------|-------|-------|
| 998 | 1-1/4" – 3" | 1/2" | 20 | 18 | 4.125" | 9.75" | 1.25" |

UTILITY SERVICE DROP, FORK BOLT BRACKETS

STEEL



FBL

FEATURES

- 10" bolt
- High strength construction

APPLICATIONS

- Use to provide attachment points for miscellaneous drop wire clamps on buildings with deep walls

STANDARD MATERIAL

- Steel

STANDARD FINISH

- Hot dipped galvanized

| PART # | BOLT LENGTH | DESCRIPTION | MASTER QTY. |
|--------|-------------|--|-------------|
| FB | 12" | FOR K BOLT BRACKETS FOR POWER LINE SUPPORT | 10 |

UTILITY SERVICE DROP, MOUNTING PLATE

STEEL



SDP

FEATURES

- .59" diameter mounting hole and slot opening

APPLICATIONS

- Bolts to exterior of building structure providing attachment point for drop wire clamps

STANDARD MATERIAL

- Steel

STANDARD FINISH

- Hot dipped galvanized

| PART # | DESCRIPTION | MASTER QTY. |
|--------|-----------------------------|-------------|
| SDP | SERVICE DROP MOUNTING PLATE | 10 |

UTILITY POLE CONDUIT SUPPORT STAND-OFF BRACKET

STEEL



SOB-1

FEATURES

- 60" diameter pole mounting holes
- Clamping action stabilizes conduit on utility pole

APPLICATIONS

- Secures 2" to 6" conduit vertically to utility pole

STANDARD MATERIAL

- Steel

STANDARD FINISH

- Hot dipped galvanized


| PART # | DESCRIPTION | MASTER QTY. |
|--------|------------------------------|-------------|
| SOB-1 | UTILITY POLE CONDUIT SUPPORT | 10 |

WATERTIGHT CONNECTORS

FOR UF CABLE



871



FEATURES

- Compression type
- Rubber grommet

APPLICATIONS

- Use to secure SE/SEU cable to a metal enclosure
- Use to connect UF cable to a waterproof box with a threaded hub
- For SE/SEU flat style cable; two insulating conductors

STANDARD MATERIAL

- Steel or zinc

CERTIFICATIONS


- UL

| PART # | SIZE | WIRE SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | GROMMET OPENING | | C |
|--------------|------------|-----------|------------|-------------|---------------------|-----------------|---|--------|
| | | | | | | A | B | |
| ZINC | | | | | | | | |
| 871 | 1/2" | 2#14 | 25 | 250 | 43 | .22" x .44" | | 1.437" |
| 872TZ | 3/4" | 3#14 | 25 | 250 | 65 | .22" x .44" | | 1.75" |
| STEEL | | | | | | | | |
| 871S | | | | | | | | |
| 872S | 3/4" STEEL | 3#14 | 25 | 250 | 45 | .22" x .44" | | 1.75" |

COMPRESSION TYPE



873



FEATURES

- Compression type
- Rubber grommet

APPLICATIONS

- Use to secure SE/SEU cable to a metal enclosure
- For SE/SEU flat style cable; two insulating conductors

STANDARD MATERIAL

- Zinc die cast


CERTIFICATIONS

- UL, CSA


| PART # | SIZE | WIRE SIZE | INNER QTY. | MASTER QTY. | WEIGHT/ CASE (LBS.) | GROMMET OPENING | | C |
|--------|--------|-----------|------------|-------------|---------------------|-----------------|--------|-------|
| | | | | | | A | B | |
| 873 | 1" | 3#8 | 10 | 100 | 34 | 0.400" | 0.630" | 1.56" |
| 873A | 1" | 3#6 | 10 | 100 | 34 | 0.440" | 0.700" | 1.56" |
| 873B | 1" | 3#4 | 10 | 100 | 34 | 0.500" | 0.800" | 1.56" |
| 874 | 1-1/4" | 3#3 | 10 | 100 | 52 | 0.510" | 0.850" | 1.99" |
| 874A | 1-1/4" | 3#2 | 10 | 100 | 52 | 0.570" | 0.940" | 1.99" |
| 874B | 1-1/4" | 3#1 | 10 | 100 | 52 | 0.660" | 1.120" | 1.99" |
| 875 | 1-1/2" | 3#1/0 | 5 | 50 | 33 | 0.705" | 1.195" | 2.18" |
| 875A | 1-1/2" | 3#2/0 | 5 | 50 | 32 | 0.740" | 1.240" | 2.18" |
| 876 | 2" | 3#1/0 | 5 | 50 | 44 | 0.705" | 1.195" | 2.41" |
| 876A | 2" | 3#2/0 | 5 | 50 | 44 | 0.740" | 1.240" | 2.41" |
| 876B | 2" | 3#3/0 | 5 | 50 | 44 | 0.830" | 1.415" | 2.41" |
| 876C | 2" | 3#4/0 | 5 | 50 | 44 | 0.890" | 1.540" | 2.41" |
| 876D | 2" | 3#4/0 | 5 | 50 | 44 | 0.990" | 1.580" | 2.41" |

CONDUIT SUPPORTS

ALUMINUM LAG SCREW TYPE



1000



FEATURES

- Accommodates conduit sizes of 2" or 2-1/2"
- Includes lag screw

APPLICATIONS

- Affixes conduit to a structure or line pole

STANDARD MATERIAL


- Aluminum

| PART # | CONDUIT SIZE | LAG | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|--------------|-------|-------------|---------------------|--------|-------|
| 1000 | 2" | 2.375 | 25 | 15 | 2.875" | .875" |
| 1000A | 2-1/2" | 2.75 | 25 | 26 | 3.30" | .875" |

MALLEABLE IRON LAG SCREW TYPE



1106



FEATURES

- Accommodates conduit sizes of 2" or 2-1/2"
- Includes lag screw

APPLICATIONS

- Affixes conduit to a structure or line pole

STANDARD MATERIAL


- Malleable iron

| PART # | CONDUIT SIZE | LAG | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|--------------|-------|-------------|---------------------|--------|-------|
| 1106 | 2" | 2.375 | 25 | 32 | 2.70" | .985" |
| 1107 | 2-1/2" | 2.375 | 35 | 87 | 3.295" | 1.08" |

SPLIT RING



1097A



FEATURES

- Accommodates conduit sizes of 2" or 4"
- Includes lag screw

APPLICATIONS

- Affixes conduit to a structure or line pole

STANDARD MATERIAL

- Malleable iron

| PART # | CONDUIT SIZE | BOLT SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) | A | B |
|--------|--------------|------------|-------------|---------------------|--------|--------|
| 1097A | 2" | 1/2" - 10" | 25 | 12 | 2.70" | .985" |
| 1097 | 2-1/2" | 1/2" - 10" | 25 | 13 | 3.33" | 1.071" |
| 1098 | 3" | 5/8" - 13" | 10 | 25 | 4.50" | 1.04" |
| 1099 | 3-1/2" | 5/8" - 13" | 10 | 27 | 5.125" | 1.075" |
| 1100 | 4" | 5/8" - 13" | 10 | 28 | 5.593" | 1.075" |

SERVICE ENTRANCE MAST KITS

FEATURES

- Accommodates multiple specifications
- Kits eliminate need to purchase and stock additional components

APPLICATIONS

- Provides an assortment of SE mast components for the installation of overhead service drops

2" KIT



736

986TZ

1008

1106

| PART # | PIPE SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) |
|------------------------------------|-----------|-------------|---------------------|
| 1966 | 2" | 1 | 4 |
| CONSISTS OF 736, 986TZ, 1008, 1106 | | | |

2-1/2" KIT



737

987

999

1107

| PART # | PIPE SIZE | MASTER QTY. | WEIGHT/ CASE (LBS.) |
|------------------------------------|-----------|-------------|---------------------|
| 1977TZ | 2-1/2" | 1 | 4 |
| CONSISTS OF 737, 987, 999, (2)1107 | | | |



Southwire™

SERVICE ENTRANCE CATALOG

get social with us:



/SOUTHWIRETOOLS



/SOUTHWIRE-COMPANY



@SOUTHWIRETOOLS



@SOUTHWIRE



SCAN TO LEARN MORE

WWW.SOUTHWIRE.COM | 1-855-SWTOOLS

All Trademarks or Registered Trademarks (TM/®) are owned or licensed by Southwire Company.
Any other TM/®- Trademark or Registered Trademark of Southwire Company.